

M12 male 0° / M12 female 0° A-cod.

PVC 8x0.25 bk UL/CSA 10m

Male straight – female straight  
M12 – M12, 8-pole  
Art-No. 7005 - M12 Lite - (plastic hexagonal screw) on request  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.  
Further cable lengths on request.

Link do produto

Ilustração



|   |    |   |
|---|----|---|
| 1 | WH | 1 |
| 2 | BN | 2 |
| 3 | GN | 3 |
| 4 | YE | 4 |
| 5 | GY | 5 |
| 6 | PK | 6 |
| 7 | BU | 7 |
| 8 | RD | 8 |





Produto pode diferir da imagem



|                                |                   |
|--------------------------------|-------------------|
| Cable length                   | 10 m              |
| Side 1                         |                   |
| Mounting method                | inserted, screwed |
| Coating contact                | gold plated       |
| Family construction form       | M12               |
| Material contact               | Copper alloy      |
| No. of poles                   | 8                 |
| Side 2                         |                   |
| Mounting method                | inserted, screwed |
| Coating contact                | gold plated       |
| Family construction form       | M12               |
| Material contact               | Copper alloy      |
| No. of poles                   | 8                 |
| Dados comerciais               |                   |
| ECLASS-6.0                     | 27279218          |
| ECLASS-6.1                     | 27279218          |
| ECLASS-7.0                     | 27279218          |
| ECLASS-8.0                     | 27279218          |
| ECLASS-9.0                     | 27060311          |
| ECLASS-10.1                    | 27060311          |
| ECLASS-11.1                    | 27060311          |
| ECLASS-12.0                    | 27060311          |
| ETIM-5.0                       | EC001855          |
| Classificação fiscal           | 85444290          |
| GTIN                           | 4048879680547     |
| Quantidade por embalagem       | 1                 |
| Electrical data   Supply       |                   |
| Operating voltage AC max.      | 30 V              |
| Operating voltage DC max.      | 30 V              |
| Device protection   Electrical |                   |
| Pollution Degree               | 3                 |

As informações contidas nesta folha de dados foram elaboradas com o máximo cuidado.  
A falta de integridade, exatidão e atualização das informações é considerada negligência grave. versão: 25/04/2024

|                                                         |                                                      |
|---------------------------------------------------------|------------------------------------------------------|
| Rated surge voltage                                     | 0,8 kV                                               |
| Material group (IEC 60664-1)                            | I                                                    |
| <b>Environmental characteristics   Climatic</b>         |                                                      |
| Operating temperature min.                              | -25 °C                                               |
| Operating temperature max.                              | 85 °C                                                |
| Additional condition temperature range                  | depending on cable quality                           |
| <b>Installation   Cable</b>                             |                                                      |
| Cable identification                                    | 607                                                  |
| Cable Type                                              | 1                                                    |
| Jacket Color                                            | black                                                |
| Type of Certificate                                     | cURus                                                |
| Amount stranding                                        | 1                                                    |
| Stranding                                               | 8 wires around Core filler twisted                   |
| Filler                                                  | yes                                                  |
| wire arrangement                                        | brown, white, red, blue, pink, gray, yellow, green   |
| Cable weight                                            | 58,3 g/m                                             |
| Material jacket                                         | PVC                                                  |
| Shore hardness jacket                                   | 85 ± 5 Shore A                                       |
| Freedom from ingredients (jacket)                       | lead-free, cadmium-free, CFC-free, silicone-free     |
| Outer-diameter (jacket)                                 | 6 mm                                                 |
| Tolerance outer diameter (sheath)                       | ± 5 %                                                |
| Material wire insulation                                | PVC                                                  |
| Amount wires                                            | 8                                                    |
| Outer diameter insulation                               | 1,2 mm                                               |
| Outer diameter tolerance core insulation                | ± 5 %                                                |
| Shore hardness wire insulation                          | 45 ± 5 Shore D                                       |
| Material properties wire insulation                     | good machinability                                   |
| Ingredient freeness wire insulation                     | lead-free, cadmium-free, CFC-free, silicone-free     |
| Amount strands (wire)                                   | 32                                                   |
| Diameter of single wires                                | 0,1 mm                                               |
| Conductor crosssection (wire)                           | 0,25 mm²                                             |
| Material conductor wire                                 | Stranded copper wire, bare                           |
| Conductor type (wire)                                   | strand class 6                                       |
| Current load capacity (standard)                        | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                         | 3 A                                                  |
| Electrical resistance line constant wire                | 79 Ω/km @ 20 °C                                      |
| Nominal voltage power AC max.                           | 300 V                                                |
| Power frequency withstand voltage power (wire - jacket) | 2 kV @ 60 s                                          |
| AC withstand voltage power (wire - wire)                | 2 kV @ 60 s                                          |
| Min. operating temperature (static)                     | -30 °C                                               |
| Max. operating temperature (fixed)                      | 80 °C                                                |
| Operating temperature min. (dynamic)                    | -5 °C                                                |
| Operating temperature max. (dynamic)                    | 80 °C                                                |
| UV resistance                                           | DIN EN ISO 4892-2 A                                  |
| Flame resistance                                        | UL 1581 § 1100 FT2   UL 1581 § 1090   IEC 60332-2-2  |
| chemical resistance                                     | Good, application-related testing                    |
| Gasoline resistance                                     | Good, application-related testing                    |
| Oil resistance                                          | Good, application-related testing   DIN EN 60811-404 |
| Bending radius (fixed)                                  | 5 x Outer diameter                                   |
| Bending radius (dynamic)                                | 10 x Outer diameter                                  |