

**M8 male 0° / M8 female 0° A-cod.**

PUR 3x0.25 bk UL/CSA 2.2m

**⚠ NOTICE ⚠****PRODUCT IS DISCONTINUED. PLEASE HAVE A LOOK AT THE ALTERNATIVE PRODUCTS.**

Male straight – female straight




M8 – M8, 3-pole

Art-No. 7005 - M12 Lite - (plastic hexagonal screw) on request

Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link do produto](#)**Ilustração**



Produto pode diferir da imagem



|                                           |                   |
|-------------------------------------------|-------------------|
| Cable length                              | 2,2 m             |
| Side 1                                    |                   |
| Tightening torque                         | 0,4 Nm            |
| Mounting method                           | inserted, screwed |
| Coating contact                           | gold plated       |
| Family construction form                  | M8                |
| Thread                                    | M8 x 1            |
| suitable for corrugated tube (internal Ø) | 6,5 mm            |
| Material contact                          | Copper alloy      |
| No. of poles                              | 3                 |
| Width across flats                        | SW9               |
| Side 2                                    |                   |
| Tightening torque                         | 0,4 Nm            |
| Mounting method                           | inserted, screwed |
| Coating contact                           | gold plated       |
| Family construction form                  | M8                |
| Thread                                    | M8 x 1            |
| Material contact                          | Copper alloy      |
| No. of poles                              | 3                 |
| Dados comerciais                          |                   |
| ECLASS-6.0                                | 27279218          |
| ECLASS-6.1                                | 27279218          |
| ECLASS-7.0                                | 27279218          |
| ECLASS-8.0                                | 27279218          |
| ECLASS-9.0                                | 27060311          |
| ECLASS-10.1                               | 27060311          |
| ECLASS-11.1                               | 27060311          |
| ECLASS-12.0                               | 27060311          |
| ETIM-5.0                                  | EC001855          |
| Classificação fiscal                      | 85444290          |
| GTIN                                      | 4048879329477     |
| Quantidade por embalagem                  | 1                 |

| Electrical data   Supply                 |                                                  |
|------------------------------------------|--------------------------------------------------|
| Operating voltage AC max.                | 50 V                                             |
| Operating voltage DC max.                | 60 V                                             |
| Operating voltage AC (UL-listed)         | 30 V                                             |
| Operating voltage DC (UL-listed)         | 30 V                                             |
| Current operating per contact max.       | 4 A                                              |
| Diagnostics                              |                                                  |
| Status indication LED                    | no                                               |
| Device protection   Electrical           |                                                  |
| Degree of protection (EN IEC 60529)      | IP65, IP67, IP68, IP66K                          |
| Additional condition protection degree   | inserted, screwed                                |
| Pollution Degree                         | 3                                                |
| Rated surge voltage                      | 1,5 kV                                           |
| Material group (IEC 60664-1)             | I                                                |
| Mechanical data   Material data          |                                                  |
| Coating locking                          | Nickeled                                         |
| Material gasket                          | FKM                                              |
| Material housing                         | PUR                                              |
| Locking material                         | Zinc die-casting                                 |
| Mechanical data   Mounting data          |                                                  |
| Mounting method                          | inserted, screwed, Shaking protection            |
| Environmental characteristics   Climatic |                                                  |
| Operating temperature min.               | -25 °C                                           |
| Operating temperature max.               | 85 °C                                            |
| Additional condition temperature range   | depending on cable quality                       |
| Conformity                               |                                                  |
| Product standard                         | DIN EN 61076-2-114 (M8)                          |
| Installation   Cable                     |                                                  |
| Cable identification                     | 620                                              |
| Cable Type                               | 2                                                |
| Jacket Color                             | black                                            |
| Type of Certificate                      | cURus                                            |
| Amount stranding                         | 1                                                |
| Stranding                                | 3 wires twisted                                  |
| wire arrangement                         | brown, black, blue                               |
| No. of bending cycles (C-track)          | 2 Mio. @ 25 °C                                   |
| Cable weight                             | 26,62 g/m                                        |
| Material jacket                          | PUR                                              |
| Shore hardness jacket                    | 85 ± 5 Shore A                                   |
| Freedom from ingredients (jacket)        | lead-free, cadmium-free, CFC-free, silicone-free |
| Outer-diameter (jacket)                  | 4,3 mm                                           |
| Tolerance outer diameter (sheath)        | ± 5 %                                            |
| Material wire insulation                 | PVC                                              |
| Amount wires                             | 3                                                |
| Outer diameter insulation                | 1,25 mm                                          |
| Outer diameter tolerance core insulation | ± 5 %                                            |
| Shore hardness wire insulation           | 43 ± 5 Shore D                                   |
| Material properties wire insulation      | good machinability                               |
| Ingredient freeness wire insulation      | lead-free, cadmium-free, CFC-free, silicone-free |
| Amount strands (wire)                    | 32                                               |
| Diameter of single wires                 | 0,1 mm                                           |

|                                                         |                                                      |
|---------------------------------------------------------|------------------------------------------------------|
| Conductor crosssection (wire)                           | 0,25 mm <sup>2</sup>                                 |
| Material conductor wire                                 | Stranded copper wire, bare                           |
| Conductor type (wire)                                   | strand class 6                                       |
| Traversing distance (C-track)                           | 5 m @ 25 °C   horizontal                             |
| Current load capacity (standard)                        | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                         | 4,5 A                                                |
| Electrical resistance line constant wire                | 79 Ω/km @ 20 °C                                      |
| Nominal voltage power AC max.                           | 300 V                                                |
| Power frequency withstand voltage power (wire - jacket) | 2 kV @ 60 s                                          |
| AC withstand voltage power (wire - wire)                | 2 kV @ 60 s                                          |
| Min. operating temperature (static)                     | -30 °C                                               |
| Max. operating temperature (fixed)                      | 80 °C                                                |
| Operating temperature min. (dynamic)                    | -5 °C                                                |
| Operating temperature max. (dynamic)                    | 80 °C                                                |
| UV resistance                                           | DIN EN ISO 4892-2 A                                  |
| Flame resistance                                        | IEC 60332-2-2   UL 1581 § 1100 FT2   UL 1581 § 1090  |
| chemical resistance                                     | Good, application-related testing                    |
| Gasoline resistance                                     | Good, application-related testing                    |
| Oil resistance                                          | DIN EN 60811-404   Good, application-related testing |
| Bending radius (fixed)                                  | 10 x Outer diameter                                  |
| Bending radius (dynamic)                                | 15 x Outer diameter                                  |