

**M8 panel feed through male / female 0° A-cod.**

3-pol., shielded

Artigo Nº: 7000-88111-000000

Peso: 0.035

País de origem: DE

Designação do modelo: MSFL0-H-R Schaltschrankdurchführung




Control cabinet entry system


Male - female

M8, 3-pole

Rear mounting

shielded

**[Link do produto](#)****Ilustração**



Produto pode diferir da imagem

Side 1	
Family construction form	M8
Material contact	Copper alloy
No. of poles	4
Dados comerciais	
ECLASS-6.0	27143423
ECLASS-7.0	27449001
ECLASS-8.0	27449001
ECLASS-9.0	27440321
ECLASS-10.1	27440109
ECLASS-11.1	27440109
ECLASS-12.0	27440109
ETIM-5.0	EC002640
Classificação fiscal	85366990
Classificação fiscal	85366990
EAN	4048879689298
EAN	4048879689298
Quantidade por embalagem	1
Quantidade por embalagem	1
Electrical data   Supply	
Operating voltage DC	30 V
Current operating per contact max.	4 A
Diagnostics	
Status indication LED	no
Installation   Connection	
Mating cycles min.	100
Device protection   Electrical	
Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	2,5 kV
Overvoltage category (EN 60950-1)	II
Mechanical data	
Contour for corrugated hose	without
Mechanical data   Material data	
Material housing	Metal

Coating contact	gold plated
Material contact carrier	PA
<b>Mechanical data   Mounting data</b>	
Mounting method	inserted, screwed
<b>Environmental characteristics   Climatic</b>	
Operating temperature min.	-25 °C
Operating temperature max.	85 °C
<b>Important installation notes</b>	
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	<b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.