

M8 panel feed through male / female 0° A-cod.

4-pol., shielded




Control cabinet entry system


Male - female

M8, 4-pole

Rear mounting

shielded

[Link do produto](#)**Ilustração**



Produto pode diferir da imagem

Side 1	
Family construction form	M8
Material contact	Copper alloy
No. of poles	4
Dados comerciais	
ECLASS-6.0	27143423
ECLASS-7.0	27449001
ECLASS-8.0	27449001
ECLASS-9.0	27440321
ECLASS-10.1	27440109
ECLASS-11.1	27440109
ECLASS-12.0	27440109
ETIM-5.0	EC002640
Classificação fiscal	85366990
GTIN	4048879689304
Quantidade por embalagem	1
Electrical data Supply	
Operating voltage DC	60 V
Current operating per contact max.	4 A
Diagnostics	
Status indication LED	no
Installation Connection	
Mating cycles min.	100
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	1,5 kV
Overvoltage category (EN 60950-1)	II
Mechanical data	
Contour for corrugated hose	without
Mechanical data Material data	
Coating contact	gold plated
Material housing	Metal
Material contact carrier	PA

As informações contidas nesta folha de dados foram elaboradas com o máximo cuidado.
A falta de integridade, exatidão e atualização das informações é considerada negligência grave. versão: 17/05/2024

Mechanical data | Mounting data

Mounting method	inserted, screwed
-----------------	-------------------

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	85 °C

Important installation notes

Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.