

**MSUD valve plug C-8mm with cable**

PUR 3x0.75 ye UL/CSA+drag ch. 10m

MSUD

Form C (8 mm)





24 V AC/DC  $\pm 25\%$ 

LED

Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link do produto](#)**Ilustração**

Produto pode diferir da imagem



Cable length 10 m

**Side 1**

Tightening torque 0,4 Nm

Thread M2.5

| Dados comerciais                         |                                                                |
|------------------------------------------|----------------------------------------------------------------|
| ECLASS-6.0                               | 27279218                                                       |
| ECLASS-6.1                               | 27279218                                                       |
| ECLASS-7.0                               | 27279218                                                       |
| ECLASS-8.0                               | 27279218                                                       |
| ECLASS-9.0                               | 27060312                                                       |
| ECLASS-10.1                              | 27060312                                                       |
| ECLASS-11.1                              | 27060312                                                       |
| ECLASS-12.0                              | 27060312                                                       |
| ETIM-5.0                                 | EC001855                                                       |
| Classificação fiscal                     | 85444290                                                       |
| GTIN                                     | 4048879641487                                                  |
| Quantidade por embalagem                 | 1                                                              |
| Electrical data   Supply                 |                                                                |
| Operating voltage AC                     | 24 V                                                           |
| Operating voltage AC min.                | 18 V                                                           |
| Operating voltage AC max.                | 30 V                                                           |
| Operating voltage DC                     | 24 V                                                           |
| Operating voltage DC min.                | 18 V                                                           |
| Operating voltage DC max.                | 30 V                                                           |
| Current operating per contact max.       | 4 A                                                            |
| Device protection   Electrical           |                                                                |
| Degree of protection (EN IEC 60529)      | IP67                                                           |
| Additional condition protection degree   | inserted, screwed                                              |
| Mechanical data   Material data          |                                                                |
| Color housing                            | black                                                          |
| Material housing                         | Plastic                                                        |
| Mechanical data   Mounting data          |                                                                |
| Mounting method                          | inserted, screwed                                              |
| Environmental characteristics   Climatic |                                                                |
| Operating temperature min.               | -25 °C                                                         |
| Operating temperature max.               | 85 °C                                                          |
| Additional condition temperature range   | depending on cable quality                                     |
| Installation   Cable                     |                                                                |
| Cable identification                     | 036                                                            |
| Cable Type                               | 3                                                              |
| Printing color of wire insulation        | white (isolation black)                                        |
| Jacket Color                             | yellow                                                         |
| Type of Certificate                      | cURus                                                          |
| Amount stranding                         | 1                                                              |
| Stranding                                | 3 wires twisted                                                |
| wire arrangement                         | black 1, black 2, green-yellow                                 |
| No. of bending cycles (C-track)          | 10 Mio. @ 25 °C                                                |
| Cable weight                             | 56,1 g/m                                                       |
| Material jacket                          | PUR                                                            |
| Shore hardness jacket                    | 90 ± 5 Shore A                                                 |
| Freedom from ingredients (jacket)        | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Outer-diameter (jacket)                  | 5,9 mm                                                         |
| Tolerance outer diameter (sheath)        | ± 5 %                                                          |
| Material wire insulation                 | PP                                                             |

|                                                         |                                                                |
|---------------------------------------------------------|----------------------------------------------------------------|
| Amount wires                                            | 3                                                              |
| Outer diameter insulation                               | 1,85 mm                                                        |
| Outer diameter tolerance core insulation                | ± 5 %                                                          |
| Shore hardness wire insulation                          | 70 ± 5 Shore D                                                 |
| Ingredient freeness wire insulation                     | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Printing color of wire insulation                       | white (isolation black)                                        |
| Amount strands (wire)                                   | 42                                                             |
| Diameter of single wires                                | 0,15 mm                                                        |
| Conductor crosssection (wire)                           | 0,75 mm <sup>2</sup>                                           |
| Material conductor wire                                 | Stranded copper wire, bare                                     |
| Conductor type (wire)                                   | strand class 6                                                 |
| Traversing distance (C-track)                           | 10 m @ 25 °C   horizontal                                      |
| Current load capacity (standard)                        | to DIN VDE 0298-4                                              |
| Current load capacity min. wire                         | 12 A                                                           |
| Electrical resistance line constant wire                | 26 Ω/km @ 20 °C                                                |
| Nominal voltage power AC max.                           | 300 V                                                          |
| Power frequency withstand voltage power (wire - jacket) | 2,5 kV @ 60 s                                                  |
| AC withstand voltage power (wire - wire)                | 2,5 kV @ 60 s                                                  |
| Min. operating temperature (static)                     | -40 °C                                                         |
| Max. operating temperature (fixed)                      | 80 °C / 90 °C @ 10000 h Operation                              |
| Operating temperature min. (dynamic)                    | -25 °C                                                         |
| Operating temperature max. (dynamic)                    | 80 °C / 90 °C @ 10000 h Operation                              |
| Flame resistance                                        | UL 1581 § 1100 FT2   UL 1581 § 1090   IEC 60332-2-2            |
| chemical resistance                                     | Good, application-related testing                              |
| Gasoline resistance                                     | Good, application-related testing                              |
| Oil resistance                                          | Good, application-related testing   DIN EN 60811-404           |
| Bending radius (fixed)                                  | 5 x Outer diameter                                             |
| Bending radius (dynamic)                                | 10 x Outer diameter                                            |
| No. of torsion cycles                                   | 2 Mio.                                                         |
| Torsion speed                                           | 35 cycles/min                                                  |
| Torsion stress                                          | ± 180 °/m                                                      |