

**M12 female 0° A-cod. with cable V2A**

PUR 4x0.34 gy UL/CSA 10m

**⚠ NOTICE ⚠****PRODUCT IS DISCONTINUED. PLEASE HAVE A LOOK AT THE ALTERNATIVE PRODUCTS.**

Female straight

M12, 4-pole




Art-No. 7005 - M12 Lite - (plastic hexagonal screw) on request

Stainless steel 1.4305 (V2A)

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

**Link do produto****Ilustração**

Produto pode diferir da imagem



Cable length 10 m

#### Side 1

|                                           |             |
|-------------------------------------------|-------------|
| Tightening torque                         | 0,6 Nm      |
| Family construction form                  | M12         |
| Thread                                    | M12 x 1     |
| suitable for corrugated tube (internal Ø) | 10 mm       |
| Width across flats                        | SW13        |
| Degree of protection (EN IEC 60529)       | IP66K, IP67 |

#### Dados comerciais

|                          |               |
|--------------------------|---------------|
| ECLASS-6.0               | 27279218      |
| ECLASS-6.1               | 27279218      |
| ECLASS-7.0               | 27279218      |
| ECLASS-8.0               | 27279218      |
| ECLASS-9.0               | 27060311      |
| ECLASS-10.1              | 27060311      |
| ECLASS-11.1              | 27060311      |
| ECLASS-12.0              | 27060311      |
| ETIM-5.0                 | EC001855      |
| Classificação fiscal     | 85444290      |
| GTIN                     | 4048879819985 |
| Quantidade por embalagem | 1             |

#### Electrical data | Supply

|                                    |       |
|------------------------------------|-------|
| Operating voltage AC max.          | 250 V |
| Operating voltage DC max.          | 250 V |
| Operating voltage AC (UL-listed)   | 30 V  |
| Operating voltage DC (UL-listed)   | 30 V  |
| Current operating per contact max. | 4 A   |

#### Device protection | Electrical

|                                        |                   |
|----------------------------------------|-------------------|
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Material group (IEC 60664-1)           | I                 |

#### Mechanical data | Material data

|                  |                              |
|------------------|------------------------------|
| Material housing | PUR                          |
| Locking material | Stainless steel 1.4305 (V2A) |

#### Mechanical data | Mounting data

|                 |                                       |
|-----------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
|-----------------|---------------------------------------|

#### Environmental characteristics | Climatic

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

#### Conformity

|                  |                          |
|------------------|--------------------------|
| Product standard | DIN EN 61076-2-101 (M12) |
|------------------|--------------------------|

#### Cable

|                      |                                            |
|----------------------|--------------------------------------------|
| Cable identification | 224                                        |
| Cable Type           | 2 (PUR/PVC)                                |
| Approval (cable)     | UL (AWM-Style 20549/1731), CSA; CE conform |
| Cable weight [g/m]   | 42,68 g                                    |
| Material wire        | Cu wire, bare                              |
| Resistor (core)      | max. 57 Ω/km (20 °C)                       |
| Single wire Ø (core) | 0.1 mm                                     |

|                                   |                                                                                                                                                        |
|-----------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| Construction (core)               | 42× 0.1 mm (multi-strand wire class 6)                                                                                                                 |
| Diameter (core)                   | 4× 0.34 mm <sup>2</sup>                                                                                                                                |
| AWG                               | similar to AWG 22                                                                                                                                      |
| Material wire isolation           | PVC                                                                                                                                                    |
| Material property wire insulation | CFC-, cadmium-, silicone- and lead-free                                                                                                                |
| Shore hardness wire isolation     | 43 ±5 D                                                                                                                                                |
| Wire-Ø incl. isolation            | 1.25 mm ±5%                                                                                                                                            |
| Color/numbering of wires          | br, bk, bl, wh                                                                                                                                         |
| Stranding combination             | 4 wires twisted                                                                                                                                        |
| Shield                            | no                                                                                                                                                     |
| Material jacket                   | PUR/PVC                                                                                                                                                |
| Material property (jacket)        | CFC-, halogen-, cadmium-, silicone- and lead-free, matt, low-adhesion, machine easy to process, abrasion-resistant, hydrolysis and microbial resistant |
| Shore hardness jacket             | 80 ±5 A (PVC-under jacket); 85 ±5 A (PUR-jacket)                                                                                                       |
| Outer-Ø (jacket)                  | 4.6 mm ±5%                                                                                                                                             |
| Color jacket                      | gray                                                                                                                                                   |
| chemical resistance               | good resistance to oil, gasoline and chemicals                                                                                                         |
| Nominal voltage                   | UL 300 V AC                                                                                                                                            |
| Test voltage                      | 2000 V AC                                                                                                                                              |
| Current load capacity             | to DIN VDE 0298-4                                                                                                                                      |
| Temperature range (fixed)         | -30...+80 °C                                                                                                                                           |
| Temperature range (mobile)        | -5...+80 °C                                                                                                                                            |
| Bending radius (fixed)            | 10× outer Ø                                                                                                                                            |
| Bending radius (dynamic)          | 15× outer Ø                                                                                                                                            |
| No. of bending cycles (C-track)   | max. 2 Mio. (25 °C)                                                                                                                                    |
| Travel speed (C-track)            | max. 3.3 m/s                                                                                                                                           |
| Acceleration (C-track)            | max. 5 m/s <sup>2</sup>                                                                                                                                |