


GBIT module - male, crimp t.

Male
Gigabit
Technical data will be only guaranteed with Murrelektronik components.
The clip 70MH-ZZ100-0000000 is needed (2×)

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	27143424
ECLASS-6.1	27261204
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
Classificação fiscal	85389099
GTIN	4048879664028
Quantidade por embalagem	1
Electrical data Supply	
Operating voltage AC	50 V
Operating voltage DC	50 V
Operating current	5 A
Industrial communication	
Transfer parameters	CAT6A
Installation	
Connection cross section min.	0,08 mm²
Connection cross section max.	0,5 mm²

AWG number min.	28
AWG number max.	20
Installation Connection	
Stripping length	4,2 mm
Wire insulation diameter min.	5 mm
Wire insulation diameter max.	7 mm
Connection	Crimp
Gender	male
Mating cycles min.	500
Installation Pin assignment	
No. of poles	8
Device protection Electrical	
Pollution Degree	3
Rated surge voltage	0,8 kV
Overvoltage category (EN 60950-1)	III
Mechanical data Material data	
Combustibility class (UL94)	V-0
Material housing	PC
Mechanical data Mounting data	
Number of module slots	1
Height	50,4 mm
Width	34,1 mm
Depth	14,6 mm
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	85 °C