

**M12 male 0° / M8 female 0°**

PUR 3x0.34 gy UL/CSA+drag chain 2,5m



Male straight – female straight

M12 – M8, 3-pole


Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

**Link do produto****Ilustração**

|   |    |   |
|---|----|---|
| 1 | BN | 1 |
|   |    | 2 |
| 3 | BU | 3 |
| 4 | BK | 4 |





Produto pode diferir da imagem



|                                        |                   |
|----------------------------------------|-------------------|
| Cable length                           | 2,5 m             |
| Side 1                                 |                   |
| Tightening torque                      | 0,6 Nm            |
| Family construction form               | M12               |
| Thread                                 | M12 x 1           |
| Degree of protection (EN IEC 60529)    | IP66K, IP67       |
| Side 2                                 |                   |
| Tightening torque                      | 0,4 Nm            |
| Family construction form               | M8                |
| Thread                                 | M8 x 1            |
| Degree of protection (EN IEC 60529)    | IP66K, IP67       |
| Dados comerciais                       |                   |
| ECLASS-6.0                             | 27279218          |
| ECLASS-7.0                             | 27279218          |
| ECLASS-8.0                             | 27279218          |
| ECLASS-9.0                             | 27060311          |
| ECLASS-10.1                            | 27060311          |
| ECLASS-11.1                            | 27060311          |
| ECLASS-12.0                            | 27060311          |
| ETIM-5.0                               | EC001855          |
| Classificação fiscal                   | 85444290          |
| GTIN                                   | 4048879538473     |
| Quantidade por embalagem               | 1                 |
| Electrical data   Supply               |                   |
| Operating voltage AC max.              | 60 V              |
| Operating voltage DC max.              | 60 V              |
| Current operating per contact max.     | 4 A               |
| Device protection   Electrical         |                   |
| Additional condition protection degree | inserted, screwed |
| Mechanical data   Material data        |                   |
| Coating locking                        | Nickeled          |

As informações contidas nesta folha de dados foram elaboradas com o máximo cuidado.  
A falta de integridade, exatidão e atualização das informações é considerada negligência grave. versão: 20/05/2024

Locking material                      Zinc die-casting

#### Mechanical data | Mounting data

Mounting method                      inserted, screwed, Shaking protection

#### Environmental characteristics | Climatic

Operating temperature min.                      -25 °C

Operating temperature max.                      85 °C

Additional condition temperature range                      depending on cable quality

#### Important installation notes

Note on strain relief                      Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Note on bending radius                      **Attention:** Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.

#### Installation | Cable

Cable identification                      233

Cable Type                      3

Jacket Color                      gray

Type of Certificate                      cURus

Amount stranding                      1

Stranding                      3 wires twisted

wire arrangement                      brown, black, blue

Cable weight                      29,7 g/m

Material jacket                      PUR

Shore hardness jacket                      90 ± 5 Shore A

Freedom from ingredients (jacket)                      lead-free, cadmium-free, CFC-free, halogen-free, silicone-free

Outer-diameter (jacket)                      4,1 mm

Tolerance outer diameter (sheath)                      ± 5 %

Material wire insulation                      PP

Amount wires                      3

Outer diameter insulation                      1,25 mm

Outer diameter tolerance core insulation                      ± 5 %

Shore hardness wire insulation                      70 ± 5 Shore D

Ingredient freeness wire insulation                      lead-free, cadmium-free, CFC-free, halogen-free, silicone-free

Amount strands (wire)                      42

Diameter of single wires                      0,1 mm

Conductor crosssection (wire)                      0,34 mm²

Material conductor wire                      Stranded copper wire, bare

Conductor type (wire)                      strand class 6

Traversing distance (C-track)                      10 m @ 25 °C | horizontal

Nominal voltage AC max.                      300 V

Current load capacity (standard)                      to DIN VDE 0298-4

Current load capacity min. wire                      6 A

Electrical resistance line constant wire                      57 Ω/km @ 20 °C

AC withstand voltage (wire - wire)                      2,5 kV @ 60 s

Power frequency withstand voltage (wire - jacket)                      2,5 kV @ 60 s

Min. operating temperature (static)                      -40 °C

Max. operating temperature (fixed)                      80 °C / 90 °C @ 10000 h Operation

Operating temperature min. (dynamic)                      -25 °C

Operating temperature max. (dynamic)                      80 °C / 90 °C @ 10000 h Operation

Flame resistance                      UL 1581 § 1090 | IEC 60332-2-2 | UL 1581 § 1100 FT2

chemical resistance                      Good, application-related testing

Gasoline resistance                      Good, application-related testing

Oil resistance                      Good, application-related testing | DIN EN 60811-404

Bending radius (fixed)                      5 x Outer diameter

|                          |                     |
|--------------------------|---------------------|
| Bending radius (dynamic) | 10 x Outer diameter |
| Travel speed (C-track)   | 10 Mio. @ 25 °C     |
| No. of torsion cycles    | 2 Mio.              |
| Torsion stress           | $\pm 180$ °/m       |
| Torsion speed            | 35 cycles/min       |