

A16 male 16-pole, Push-in, 250 V, 20 A


A16
Male
16-pole
Push-In terminals
Technical data will be only guaranteed with Murrelektronik components.
Please use wire end ferrule.

Link do produto

Ilustração



Produto pode diferir da imagem



Dados comerciais	
ECLASS-6.0	27143424
ECLASS-6.1	27261204
ECLASS-7.0	27440205
ECLASS-8.0	27440205
ECLASS-9.0	27440205
ECLASS-10.1	27440205
ECLASS-11.1	27440205
ECLASS-12.0	27440205
ETIM-5.0	EC000438
Classificação fiscal	85366990
GTIN	4048879764612
Quantidade por embalagem	1
Electrical data Supply	
Operating voltage AC	250 V
Operating voltage DC	250 V
Operating current	16 A
Installation	
Connection cross section min.	0,14 mm²
Connection cross section max.	2,5 mm²
AWG number min.	26

AWG number max. 14

Installation | Connection

Stripping length 8 mm

Connection Push-In spring clamp terminals

Gender male

Mating cycles min. 500

Installation | Pin assignment

No. of poles 16 + PE

Device protection | Electrical

Pollution Degree 3

Rated surge voltage 4 kV

Overvoltage category (EN 60950-1) III

Mechanical data | Material data

Coating contact silver-plated

Combustibility class (UL94) V-0

Material contact Copper alloy

Material contact carrier PC

Mechanical data | Mounting data

Size A16

Height 35 mm

Width 23,2 mm

Depth 72 mm

Environmental characteristics | Climatic

Operating temperature min. -40 °C

Operating temperature max. 125 °C

Climatic category (EN IEC 60068-1) 40/125/21