



M12 female 0° field-wireable

4-pole max. 0.75mm² 4-6mm

Customized printing and packaging
Female straight
M12, 4-pole
Screw terminals
Sealing range (cable Ø): 4...6 mm
Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link do produto

Ilustração



Produto pode diferir da imagem



Side 1	
Family construction form	M12
Coding	A
Material contact	Copper alloy

No. of poles	4
Degree of protection (EN IEC 60529)	IP67
Dados comerciais	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27440102
ECLASS-11.1	27440102
ECLASS-12.0	27440116
ETIM-5.0	EC001855
Classificação fiscal	85366990
GTIN	4048879848657
Quantidade por embalagem	10
Electrical data Supply	
Operating voltage AC max.	250 V
Operating voltage DC max.	250 V
Current operating per contact max.	4 A
Current operating per contact max. (URc.)	3 A
Diagnostics	
Status indication LED	no
Installation	
Connection cross section max.	0,75 mm²
Installation Connection	
Tightening torque	0,6 Nm
Mounting set	M12 x 1
Width across flats	SW18
Device protection Electrical	
Additional condition protection degree	screwed, mounted
Pollution Degree	3
Material group (IEC 60664-1)	III
Mechanical data Material data	
Coating contact	Copper alloy
Coating of fitting	nickel plated
Material housing	PA
Material screw connection	Zinc die-casting
Mechanical data Mounting data	
Mounting method	inserted, screwed, Shaking protection
Clamping range min.	4 mm
Clamping range max.	6 mm
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	85 °C
Conformity	
Product standard	DIN EN 61076-2-101 (M12)