



EXACT12, 4XM12, 4 POLE MOULDED CABLE

10.0m PUR/PVC 4X0.34+3X0.75, UL/CSA


4-way, 4-pole  
PUR/PVC  
Further cable lengths on request.  
10.0 m  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link do produto

Ilustração



Produto pode diferir da imagem



| Dados comerciais |          |
|------------------|----------|
| ECLASS-6.0       | 27279219 |
| ECLASS-6.1       | 27279219 |
| ECLASS-7.0       | 27279219 |
| ECLASS-8.0       | 27279219 |

|                          |               |
|--------------------------|---------------|
| ECLASS-9.0               | 27440108      |
| ECLASS-10.1              | 27440108      |
| ECLASS-11.1              | 27440108      |
| ECLASS-12.0              | 27440108      |
| ETIM-5.0                 | EC002585      |
| Classificação fiscal     | 85444290      |
| GTIN                     | 4048879056038 |
| Quantidade por embalagem | 1             |

**Electrical data | Supply**

|                                    |      |
|------------------------------------|------|
| Operating voltage DC               | 24 V |
| Current operating per contact max. | 4 A  |

**Installation | Connection**

|              |         |
|--------------|---------|
| Mounting set | M12 x 1 |
|--------------|---------|

**Device protection | Electrical**

|                                     |            |
|-------------------------------------|------------|
| Degree of protection (EN IEC 60529) | IP65, IP67 |
|-------------------------------------|------------|

**Device protection | Media**

|                  |                 |
|------------------|-----------------|
| Flame resistance | flame retardant |
|------------------|-----------------|

**Mechanical data | Material data**

|                  |         |
|------------------|---------|
| Material housing | Plastic |
|------------------|---------|

**Mechanical data | Mounting data**

|                 |                |
|-----------------|----------------|
| Mounting method | Schraubgewinde |
|-----------------|----------------|

**Environmental characteristics | Climatic**

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -20 °C                     |
| Operating temperature max.             | 70 °C                      |
| Additional condition temperature range | depending on cable quality |

**Installation | Cable**

|                                          |                                                       |
|------------------------------------------|-------------------------------------------------------|
| Cable identification                     | 333                                                   |
| Cable Type                               | 2                                                     |
| Jacket Color                             | gray                                                  |
| Type of Certificate                      | cURus                                                 |
| STOOW style jacket                       | Hybrid, Signal, Power                                 |
| Amount stranding                         | 1                                                     |
| Stranding                                | 7 wires around Core filler twisted                    |
| Filler                                   | yes                                                   |
| wire arrangement                         | white, green, yellow, gray, brown, blue, green-yellow |
| No. of bending cycles (C-track)          | 2 Mio.                                                |
| Cable weight                             | 105,6 g/m                                             |
| Material jacket                          | PUR                                                   |
| Shore hardness jacket                    | 87 ± 5 Shore A                                        |
| Freedom from ingredients (jacket)        | lead-free, cadmium-free, CFC-free, silicone-free      |
| Outer-diameter (jacket)                  | 7,4 mm                                                |
| Tolerance outer diameter (sheath)        | ± 5 %                                                 |
| Material inner jacket                    | PVC                                                   |
| Color (inner jacket)                     | gray                                                  |
| Material wire insulation                 | PVC                                                   |
| Amount wires                             | 4                                                     |
| Outer diameter insulation                | 1,3 mm                                                |
| Outer diameter tolerance core insulation | ± 5 %                                                 |
| Shore hardness wire insulation           | 43 ± 5 Shore D                                        |
| Material properties wire insulation      | good machinability                                    |
| Ingredient freeness wire insulation      | lead-free, cadmium-free, CFC-free, silicone-free      |

|                                                         |                                                      |
|---------------------------------------------------------|------------------------------------------------------|
| Amount strands (wire)                                   | 19                                                   |
| Diameter of single wires                                | 0,15 mm                                              |
| Conductor crosssection (wire)                           | 0,34 mm <sup>2</sup>                                 |
| Material conductor wire                                 | Stranded copper wire, bare                           |
| Conductor type (wire)                                   | Strand class 5                                       |
| Material wire insulation (Power)                        | PVC                                                  |
| Outer diameter wire insulation (Power)                  | 1,8 mm                                               |
| Tolerance outer diameter wire insulation (Power)        | ±5 %                                                 |
| Shore hardness wire insulation (Power)                  | 43±5 Shore D                                         |
| Material properties wire insulation (Power)             | good machinability                                   |
| Ingredient freeness wire insulation (Power)             | lead-free, cadmium-free, CFC-free, silicone-free     |
| Amount wires (Power)                                    | 3                                                    |
| Amount strands wire (Power)                             | 24                                                   |
| Diameter of single wires (Power)                        | 0,2 mm                                               |
| Wire conductor cross section (Power)                    | 0,75 mm <sup>2</sup>                                 |
| Material conductor wire (Power)                         | Stranded copper wire, bare                           |
| Conductor type wire (Power)                             | Strand class 5                                       |
| Traversing distance (C-track)                           | 5 m                                                  |
| Current load capacity (standard)                        | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                         | 4 A                                                  |
| Electrical resistance line constant wire                | 57 Ω/km @ 20 °C                                      |
| Electrical resistance coating wire (Power)              | 26 Ω/km @20 °C                                       |
| Loop resistance                                         | 7,8 A                                                |
| Max. rated voltage power (conductor - ground)           | 300 V                                                |
| Max. rated voltage power (conductor - conductor)        | 300 V                                                |
| Power frequency withstand voltage power (wire - jacket) | 2 kV @ 60 s                                          |
| AC withstand voltage power (wire - wire)                | 2 kV @ 60 s                                          |
| Min. operating temperature (static)                     | -30 °C                                               |
| Max. operating temperature (fixed)                      | 80 °C                                                |
| Operating temperature min. (dynamic)                    | -5 °C                                                |
| Operating temperature max. (dynamic)                    | 70 °C                                                |
| Flame resistance                                        | UL 1581 § 1100 FT2   UL 1581 § 1090   IEC 60332-2-2  |
| chemical resistance                                     | Good, application-related testing                    |
| Gasoline resistance                                     | Good, application-related testing                    |
| Oil resistance                                          | Good, application-related testing   DIN EN 60811-404 |
| Bending radius (fixed)                                  | 5 x Outer diameter                                   |
| Bending radius (dynamic)                                | 10 x Outer diameter                                  |

#### Connection type 2

|                          |                |
|--------------------------|----------------|
| Family construction form | free cable end |
| No. of poles             | 7              |
| Family construction form | M12            |
| Gender                   | female         |
| Color contact carrier    | black          |
| Coding                   | A              |
| No. of poles             | 4              |
| PIN 1                    | +              |
| PIN 2                    | n.c.           |
| PIN 3                    | -              |
| PIN 4                    | NO S 1         |
| PIN 5                    | PE             |