


MVP12, 6XM12, 5POLE, PLUGGABLE CABLE

3.0m PUR/PVC 12x0,34+5x0,75

Further cable lengths on request.  
6-way, 5-pole  
Plastic housings with good resistance against chemicals and oils.  
PUR/PVC  
The resistance to aggressive media should be individually tested for your application. Further details on request.  
3.0 m  
potentially separated  
with LED for digital PNP-signals 24 V DC

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



| 제품자료       |          |
|------------|----------|
| ECLASS-6.0 | 27279219 |
| ECLASS-6.1 | 27279219 |

|             |               |
|-------------|---------------|
| ECLASS-7.0  | 27279219      |
| ECLASS-8.0  | 27279219      |
| ECLASS-9.0  | 27440108      |
| ECLASS-10.1 | 27440108      |
| ECLASS-11.1 | 27440108      |
| ECLASS-12.0 | 27440108      |
| ETIM-5.0    | EC002585      |
| GTIN        | 4048879064279 |
| 세번부호        | 85369010      |
| 포장단위        | 1             |

Electrical data | Supply

|                                               |      |
|-----------------------------------------------|------|
| Operating voltage DC                          | 24 V |
| Operating voltage DC min.                     | 18 V |
| Operating voltage DC max.                     | 30 V |
| Current operating per contact max.            | 4 A  |
| Total current at 1 time current feed-in max.  | 8 A  |
| Total current at 2 times current feed-in max. | 16 A |

Industrial communication

|                            |   |
|----------------------------|---|
| Number of signals per port | 2 |
|----------------------------|---|

Installation | Connection

|                   |         |
|-------------------|---------|
| Tightening torque | 0,6 Nm  |
| Mounting set      | M12 x 1 |

Device protection | Electrical

|                                        |                   |
|----------------------------------------|-------------------|
| Degree of protection (EN IEC 60529)    | IP65, IP67        |
| Additional condition protection degree | inserted, screwed |

Device protection | Media

|                  |                 |
|------------------|-----------------|
| Flame resistance | flame retardant |
|------------------|-----------------|

Mechanical data | Material data

|                  |     |
|------------------|-----|
| Material housing | PBT |
|------------------|-----|

Mechanical data | Mounting data

|        |         |
|--------|---------|
| Height | 125 mm  |
| Width  | 50,2 mm |
| Depth  | 17 mm   |

Environmental characteristics | Climatic

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -20 °C                     |
| Operating temperature max.             | 80 °C                      |
| Additional condition temperature range | depending on cable quality |

Connection type 2

|                          |                |
|--------------------------|----------------|
| Family construction form | free cable end |
| Color contact carrier    | gray           |
| No. of poles             | 17             |
| Family construction form | M12            |
| Gender                   | female         |
| Color contact carrier    | black          |
| Coding                   | A              |
| No. of poles             | 5              |
| PIN 1                    | +              |
| PIN 2                    | NC S 2         |
| PIN 3                    | -              |
| PIN 4                    | NO S 1         |
| PIN 5                    | PE             |

