



MIRO TR 24VDC 24VDC 10A SK OPTO-COUPLER MODULE

IN: 53 VDC - OUT: 48 VDC / 10 A

Transistor 10 A  
24 V DC  
short-circuit and overload protected  
pulse switching  
Screw terminals

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



| 제품자료       |          |
|------------|----------|
| ECLASS-6.0 | 27371604 |
| ECLASS-6.1 | 27371604 |
| ECLASS-7.0 | 27371604 |
| ECLASS-8.0 | 27371604 |
| ECLASS-9.0 | 27371604 |

|                                          |                           |
|------------------------------------------|---------------------------|
| ECLASS-10.1                              | 27371604                  |
| ECLASS-11.1                              | 27371604                  |
| ECLASS-12.0                              | 27371604                  |
| ETIM-5.0                                 | EC001504                  |
| GTIN                                     | 4048879026796             |
| 세번부호                                     | 85414900                  |
| 포장단위                                     | 1                         |
| Electrical data   Input                  |                           |
| Input voltage OFF DC min.                | 0 V                       |
| Input voltage OFF DC max.                | 5 V                       |
| Input voltage DC min.                    | 10 V                      |
| Input voltage DC max.                    | 53 V                      |
| Current input DC                         | 10 mA                     |
| Electrical data   Output                 |                           |
| Overload resistant                       | yes                       |
| Short-circuit protected                  | yes                       |
| Switch-off delay resistive load max.     | 5000 µs                   |
| On-delay resistive load max.             | 2000 µs                   |
| Quiescent current OFF max.               | 0,025 mA                  |
| Switching frequency inductive max.       | 0,1 Hz                    |
| Switching frequency ohmic max.           | 1 Hz                      |
| Voltage switching DC min.                | 5 V                       |
| Switching voltage DC max.                | 48 V                      |
| Switching current min.                   | 1 mA                      |
| Switching current max.                   | 10 A                      |
| Voltage drop DC max.                     | 0,12 V                    |
| Diagnostics                              |                           |
| Status indication LED                    | yellow                    |
| Device protection   Electrical           |                           |
| Rated insulation voltage                 | 2750 V                    |
| Pulse switching                          | yes                       |
| Device protection   Media                |                           |
| Flame resistance                         | flame retardant           |
| Mechanical data   Material data          |                           |
| Color housing                            | black                     |
| Material housing                         | Plastic                   |
| Mechanical data   Mounting data          |                           |
| Mounting method                          | geschnappt                |
| Suitable for mounting type               | mounting rail, (EN 60715) |
| Height                                   | 78 mm                     |
| Width                                    | 6,2 mm                    |
| Depth                                    | 70 mm                     |
| Environmental characteristics   Climatic |                           |
| Operating temperature min.               | -20 °C                    |
| Operating temperature max.               | 60 °C                     |
| Connection type 4                        |                           |
| Connection                               | Screw terminals SK        |
| Family construction form                 | terminal                  |
| Gender                                   | female                    |
| Color contact carrier                    | green                     |

|                          |                    |
|--------------------------|--------------------|
| No. of poles             | 1                  |
| PIN 1                    | 13 +               |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| Color contact carrier    | green              |
| No. of poles             | 1                  |
| PIN 1                    | 14                 |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| Color contact carrier    | green              |
| No. of poles             | 1                  |
| PIN 1                    | A 1                |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| Color contact carrier    | green              |
| No. of poles             | 1                  |
| PIN 1                    | A 2                |