


SOLID67 IOL8(M8 5P) 30mm M12L 5P

SOLID67 Multiprotocol Profinet or EthernetIP


IOL8
M12 Power, 5-pole, L-coded
M8, 5-pole, B-coded
Connection cables are in the online shop under "Connection Technology".
Housing fully potted.

제품 링크

일러스트




실제 제품은 이미지와 다를 수 있습니다.
















제품자료	
ECLASS-6.0	27242604
ECLASS-6.1	27242604
ECLASS-7.0	27242604
ECLASS-8.0	27242604
ECLASS-9.0	27242604
ECLASS-10.1	27242604
ECLASS-11.1	27242604
ECLASS-12.0	27242604
ETIM-5.0	EC001599
GTIN	4048879727907
세번부호	85389099
포장단위	1

Electrical data Supply	
Norm operating voltage	EN 61131-2
Operating voltage US DC	24 V
Operating voltage UA DC	24 V
Total current UA max.	9 A
Total current US max.	9 A

Electrical data Input	
-------------------------	--

Overload resistant	yes
Short-circuit protected	yes
Type input	PNP, for 3-wire sensors or mechanical switches, IO-Link Devices
Current carrying capacity max.	0,5 A
Electrical data Output	
Overload resistant	yes
Short-circuit protected	yes
Output current per pin max.	0,5 A
Total current outputs max.	9 A
Industrial communication	
Supported protocol	PROFINET
Industrial communication Ethernet/IP	
DLR (Device Level Ring)	yes
EtherNet/IP addressing	BOOTP, DHCP, Rotary switch
Industrial communication Profinet	
Number of active connections (IO controller) max.	2
IRT (network communication)	yes
MRP client	yes
PROFINET Netload Class	II
PROFINET addressing	DCP
PROFINET conformance class	C
PROFINET specification	V2.3
Shared device/input	yes
Industrial communication IO-Link	
Automatic baudrate detection	yes
IO-Link process data length output	32 Bytes
IO-Link process data length input	32 Bytes
IO-Link revision ID	V1.1
IO-Link type	8x Master
IO-Link transmission rate	COM1, COM2, COM3
Port Class	A, B
Diagnostics	
Actuator warning	via LED and BUS
Diagnostic via BUS	per module and channel
Diagnostic via LED	per module and channel
IO-Link events	No voltage, Undervoltage supply
Short circuit diagnosis	yes
LED display	Ethernet connection/data traffic
Cable break	per port
Overload diagnosis	yes
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP67
Galvanic separation (operating voltage)	yes
Mechanical data Mounting data	
Suitable for mounting type	2-hole screw mounting
Height	43,1 mm
Width	30 mm
Depth	204 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C

Operating temperature max. 70 °C

Connection type 5	
Connection type 1	X01, X02
Connection type 2	X03
Connection type 3	X04
Connection type 4	X1-X4
Connection type 5	X5-X8
Family construction form	M12
Gender	female
Color contact carrier	green
Coding	D
No. of poles	4
PIN 1	TD +
PIN 2	RD +
PIN 3	TD -
PIN 4	RD -
Family construction form	M12
Gender	male
Color contact carrier	gray
Coding	L
No. of poles	5
PIN 1	24 V DC (US)
PIN 2	0 V (UA)
PIN 3	0 V (US)
PIN 4	24 V DC (UA)
PIN 5	FE
Family construction form	M12
Gender	female
Color contact carrier	gray
Coding	L
No. of poles	5
PIN 1	24 V DC (US)
PIN 2	0 V (UA)
PIN 3	0 V (US)
PIN 4	24 V DC (UA)
PIN 5	FE
Family construction form	M8
Gender	female
Color contact carrier	black
Coding	B
No. of poles	5
PIN 1	24 V DC
PIN 2	DI
PIN 3	0 V
PIN 4	SIO / IOL
PIN 5	n.c.
Family construction form	M8
Gender	female
Color contact carrier	black
Coding	B
No. of poles	5
PIN 1	24 V DC
PIN 2	24 V DC UA
PIN 3	0 V

PIN 4	SIO / IOL
PIN 5	0 V UA