

MASI00 I/O MODULE

4 digital inputs, 4 digital outputs


Digital inputs/outputs
DI4/DO4 - 0.2 A (AB)
IP00

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료	
ECLASS-6.0	27242604
ECLASS-7.0	27242604
ECLASS-8.0	27242604
ECLASS-9.0	27242604
ETIM-5.0	EC001599
GTIN	4048879050043
세번부호	85389091
포장단위	1
Electrical data Supply	
Bus voltage AS-Interface DC min.	26,5 V
Bus voltage AS-Interface DC max.	31,6 V
Current consumption AS-i port max.	250 mA
Current consumption max.	200 mA
Total current max.	0,2 A
Electrical data Input	
Overload resistant	yes
Short-circuit protected	yes
Type input	for standard switches
Current carrying capacity max.	0,2 A
Electrical data Output	

Switch off time in case of short circuit	50 ms
Overload resistant	yes
Short-circuit protected	yes
Output current per pin max.	0,2 A
Industrial communication Bus data	
Address setting type	Plug-in terminal
Industrial communication AS-Interface	
Profile (IO.ID.ID2)	S-7.A.7
Diagnostics	
Diagnostic	No voltage
Diagnostic via LED	per module
LED display	Ethernet connection/data traffic
Installation	
Connection cross section min.	0,2 mm²
Connection cross section max.	2,5 mm²
Installation Connection	
Connection	Screw plug-in terminals
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP00
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	43 mm
Width	15 mm
Depth	81 mm
Environmental characteristics Climatic	
Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-20 °C
Storage temperature max.	70 °C
Connection type 2	
Connection type 1	Asi Bus
Connection type 2	I / O
Connection	Screw terminals SK
Family construction form	terminal
Gender	male
Color contact carrier	green
No. of poles	2
PIN 1	A +
PIN 2	A -
Connection	Plug-in terminals RK
Family construction form	terminal
Gender	male
Color contact carrier	black
No. of poles	10
PIN 1	0 V
PIN 2	U +
PIN 3	O 0
PIN 4	I 0
PIN 5	O 1

PIN 6	I 1
PIN 7	O 2
PIN 8	I 2
PIN 9	O 3
PIN 10	I 3