

## Gateway Ethernet-IP/AS-i, 1 Master, P24

Spec. 3.0, Diagnosis Field bus, Power 24

AS-Interface/EtherNet/IP

Power 24V

Specification 3.0

Diagnostic via BUS

Current manuals, GSD/type data can be downloaded at: [www.murrelektronik.com](http://www.murrelektronik.com)

Other gateways on request.

Gateway-Singlemaster

AS-Interface data decoupling integrated

AS-Interface duplicate address detection



AS-Interface EMC detector integrated

## 제품 링크

### 일러스트



실제 제품은 이미지와 다를 수 있습니다.



### 제품자료

|             |               |
|-------------|---------------|
| ECLASS-6.0  | 27242208      |
| ECLASS-6.1  | 27242608      |
| ECLASS-7.0  | 27242608      |
| ECLASS-8.0  | 27242608      |
| ECLASS-9.0  | 27242608      |
| ECLASS-10.1 | 27242608      |
| ECLASS-11.1 | 27242608      |
| ECLASS-12.0 | 27242608      |
| ETIM-5.0    | EC001604      |
| GTIN        | 4048879496674 |
| 세번부호        | 85176200      |
| 포장단위        | 1             |

### Electrical data

|                                           |        |
|-------------------------------------------|--------|
| Rated operating current AS-Interface max. | 250 mA |
| Security level                            | PELV   |

Electrical data | Supply

|                           |        |
|---------------------------|--------|
| Operating voltage DC      | 24 V   |
| Operating voltage DC min. | 20 V   |
| Operating voltage DC max. | 30,6 V |

Industrial communication

|                    |             |
|--------------------|-------------|
| Supported protocol | EtherNet/IP |
|--------------------|-------------|

Industrial communication | AS-Interface

|                             |                                 |
|-----------------------------|---------------------------------|
| AS-i specification          | V3.0                            |
| Number of slaves max.       | 62                              |
| Diagnostic interface serial | RJ45/Fieldbus                   |
| Cycle time AS-i             | 150 µs × (number of slaves + 2) |

Installation | Connection

|                          |      |
|--------------------------|------|
| Family construction form | RJ45 |
|--------------------------|------|

Device protection | Electrical

|                                     |       |
|-------------------------------------|-------|
| Degree of protection (EN IEC 60529) | IP20  |
| Rated insulation voltage            | 500 V |

Mechanical data | Mounting data

|                            |                           |
|----------------------------|---------------------------|
| Mounting method            | geschnappt                |
| Suitable for mounting type | mounting rail, (EN 60715) |
| Height                     | 120 mm                    |
| Width                      | 85 mm                     |
| Depth                      | 83 mm                     |

Environmental characteristics | Climatic

|                            |        |
|----------------------------|--------|
| Operating temperature min. | 0 °C   |
| Operating temperature max. | 55 °C  |
| Storage temperature min.   | -25 °C |
| Storage temperature max.   | 85 °C  |

Conformity

|                  |                        |
|------------------|------------------------|
| Product standard | EN 61131-2, EN 62026-2 |
|------------------|------------------------|