


CUBE67+ BUS NODE

ProfiNet IO

Cube67+
PROFINET IO
Connection cables are in the online shop under "Connection Technology".
Housing fully potted.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료	
ECLASS-6.0	27242608
ECLASS-6.1	27242608
ECLASS-7.0	27242608
ECLASS-8.0	27242608
ECLASS-9.0	27242608
ECLASS-10.1	27242608
ECLASS-11.1	27242608
ECLASS-12.0	27242608
ETIM-5.0	EC001604
GTIN	4048879294027
세번부호	85389099
포장단위	1
Electrical data Supply	
Operating voltage DC	24 V
Current consumption max.	200 mA
Total current UA max.	8 A
Total current US max.	8 A
Industrial communication	
Machine Option Management	yes
Supported protocol	PROFINET

Industrial communication | Bus data

Address range outputs max.	1024 Bytes
Address range inputs max.	1024 Bytes

Industrial communication | Profinet

PROFINET addressing	DCP
PROFINET conformance class	B
PROFINET specification	V2.2

Industrial communication | IO-Link

Number of IO-Link master ports max.	128
-------------------------------------	-----

Diagnostics

Diagnostic	No voltage, Under voltage
Diagnostic via BUS	per module and channel
Diagnostic via LED	per module and channel
Short circuit diagnosis	yes
LED display	Ethernet connection/data traffic
Overload diagnosis	yes

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
-------------------------------------	------

Mechanical data

Number extension modules max.	32
-------------------------------	----

Mechanical data | Mounting data

Suitable for mounting type	2-hole screw mounting
Height	151 mm
Width	62 mm
Depth	40,5 mm

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-20 °C
Storage temperature max.	75 °C

Conformity

Product standard	EN 61131-2
------------------	------------

Connection type 4

Connection type 1	Bus In / Bus Out
Connection type 2	Internal system connection
Connection type 3	Power In
Connection type 4	Power Out
Mounting method	inserted, screwed
Tightening torque	0,6 Nm
Family construction form	M12
Gender	female
Color contact carrier	black
Coding	D
No. of poles	4
PIN 1	TD +
PIN 2	RD +
PIN 3	TD -
PIN 4	RD -
Family construction form	M12
Gender	female

Color contact carrier	black
Coding	A
No. of poles	6
PIN 1	24 V DC (UA)
PIN 2	24 V DC (US)
PIN 3	0 V
PIN 4	Bus internal
PIN 5	Bus internal
PIN 6	0 V
Family construction form	7/8"
Gender	male
Color contact carrier	black
No. of poles	5
PIN 1	0 V
PIN 2	0 V
PIN 3	PE
PIN 4	24 V DC (US)
PIN 5	24 V DC (UA)
Family construction form	7/8"
Gender	female
Color contact carrier	black
No. of poles	5
PIN 1	0 V
PIN 2	0 V
PIN 3	PE
PIN 4	24 V DC (US)
PIN 5	24 V DC (UA)