


CUBE20S COUNTER MODULE

2X32Bit 400Khz 45 Parameter Bytes

Counter module
2× 32 Bit
max. 400 kHz
OUTPUT: 12 Byte

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료	
ECLASS-6.0	27242605
ECLASS-6.1	27242605
ECLASS-7.0	27242605
ECLASS-8.0	27242605
ECLASS-9.0	27242605
ECLASS-10.1	27242605
ECLASS-11.1	27242605
ECLASS-12.0	27242605
ETIM-5.0	EC001601
GTIN	4048879422956
세번부호	90291000
포장단위	1
Electrical data	
Number of counters	2
Counter width	32 Bits
Counter frequency max.	400 kHz
Electrical data Supply	
Operating voltage DC	24 V
Operating voltage DC min.	20,4 V
Operating voltage DC max.	28,8 V

Current consumption max. 75 mA

Diagnostics	
Diagnostic	Under voltage
Diagnostic via BUS	per module
Diagnostic via LED	per module
Short circuit diagnosis	yes
LED display	Ethernet connection/data traffic
Overload diagnosis	yes

Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20

Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	109 mm
Width	12,9 mm
Depth	76,5 mm

Environmental characteristics Climatic	
Operating temperature min.	0 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
Storage temperature max.	70 °C

Connection type 2	
Connection type 1	Power
Connection type 2	Power
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	8
PIN 1	n.c.
PIN 2	24 V DC
PIN 3	0 V
PIN 4	24 V DC Sys
PIN 5	n.c.
PIN 6	24 V DC
PIN 7	0 V
PIN 8	0 V Sys
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	8
PIN 1	A 0
PIN 2	24 V DC
PIN 3	0 V
PIN 4	A 1
PIN 5	B 0
PIN 6	24 V DC
PIN 7	0 V
PIN 8	B 1