


RM 122/24 OUTPUT RELAY

IN: 24 VDC - OUT: 250 VAC/DC / 5 A

1 relay; 2 NO contacts/2 NC contacts  
5 A  
24 V DC  
with force guided contacts  
Screw terminals

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



| 제품자료       |          |
|------------|----------|
| ECLASS-6.0 | 27371001 |
| ECLASS-6.1 | 27371601 |
| ECLASS-7.0 | 27371601 |
| ECLASS-8.0 | 27371601 |
| ECLASS-9.0 | 27371601 |

|             |               |
|-------------|---------------|
| ECLASS-10.1 | 27371601      |
| ECLASS-11.1 | 27371601      |
| ECLASS-12.0 | 27371601      |
| ETIM-5.0    | EC001437      |
| GTIN        | 4048879027694 |
| 세번부호        | 85364900      |
| 포장단위        | 1             |

Electrical data | Input

|                       |        |
|-----------------------|--------|
| Input voltage DC      | 24 V   |
| Input voltage DC min. | 21,6 V |
| Input voltage DC max. | 28 V   |
| Input current         | 29 mA  |

Electrical data | Output

|                                               |                                               |
|-----------------------------------------------|-----------------------------------------------|
| Utilization category DC-13 (EN IEC 60947-5-1) | 2 A @ 24 V, 0,4 A @ 110 V, 0,3 A @ 230 V      |
| Additional condition switching frequency      | with load                                     |
| Switching frequency max.                      | 0,1 Hz                                        |
| Power rating AC max.                          | 1000 VA                                       |
| Power rating DC max.                          | 50 W                                          |
| Switching voltage AC max.                     | 250 V                                         |
| Switching voltage DC max.                     | 250 V                                         |
| Switching current DC                          | 300 mA                                        |
| Switching current max.                        | 5 A                                           |
| Switching capacity AC-12 (EN IEC 60947-5-1)   | 5 A (24/110/230 V AC)                         |
| Switching capacity AC-15 (EN IEC 60947-5-1)   | 4 A (24 V AC); 3 A (110 V AC); 2 A (230 V AC) |

Diagnostics

|                       |     |
|-----------------------|-----|
| Status indication LED | red |
|-----------------------|-----|

Device protection

|                    |                |
|--------------------|----------------|
| Condition lifetime | load-dependent |
|--------------------|----------------|

Device protection | Electrical

|                     |                |
|---------------------|----------------|
| Rated surge voltage | 2,5 kV         |
| Electrical lifetime | 1000000 Cycles |

Device protection | Mechanical

|                      |                |
|----------------------|----------------|
| Mechanical endurance | 1000000 Cycles |
|----------------------|----------------|

Mechanical data

|                    |       |
|--------------------|-------|
| Drop-out time max. | 15 ms |
| Response time max. | 15 ms |
| Bounce time max.   | 2 ms  |

Mechanical data | Material data

|                  |             |
|------------------|-------------|
| Material contact | Ag Ni 10 hv |
|------------------|-------------|

Mechanical data | Mounting data

|                            |                                     |
|----------------------------|-------------------------------------|
| Mounting method            | geschnappt                          |
| Suitable for mounting type | Mounting rail TH35, G32, (EN 60715) |
| Height                     | 75 mm                               |
| Width                      | 22,5 mm                             |
| Depth                      | 85 mm                               |

Environmental characteristics | Climatic

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -20 °C |
| Operating temperature max. | 50 °C  |

Connection type 4

|                   |    |
|-------------------|----|
| Connection type 1 | X1 |
|-------------------|----|

|                          |                    |
|--------------------------|--------------------|
| Connection type 2        | X2                 |
| Connection type 3        | X3                 |
| Connection type 4        | X4                 |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| Color contact carrier    | green              |
| No. of poles             | 4                  |
| PIN 1                    | A 2                |
| PIN 2                    | A 2                |
| PIN 3                    | A 1                |
| PIN 4                    | A 1                |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| Color contact carrier    | green              |
| No. of poles             | 4                  |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| Color contact carrier    | green              |
| No. of poles             | 4                  |
| PIN 1                    | 24                 |
| PIN 2                    | 23                 |
| PIN 3                    | 14                 |
| PIN 4                    | 13                 |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| Color contact carrier    | green              |
| No. of poles             | 4                  |
| PIN 1                    | 31                 |
| PIN 2                    | 32                 |
| PIN 3                    | 41                 |
| PIN 4                    | 42                 |