


CUBE20S ANALOG INPUT MODULE AI4

4X16BIT (I 0(4)...20 mA)

Expansion module
AI4 - (E) I
Current

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료

ECLASS-6.0	27242601
ECLASS-6.1	27242601
ECLASS-7.0	27242601
ECLASS-8.0	27242601
ECLASS-9.0	27242601
ECLASS-10.1	27242601
ECLASS-11.1	27242601
ECLASS-12.0	27242601
ETIM-5.0	EC001596
GTIN	4048879423755
세번부호	85389099
포장단위	1

Electrical data | Supply

Idle current external max.	20 mA
Current consumption max.	60 mA
module supply	via system connection

Electrical data | Input

Working resistance max.	60 Ω
Current input mode 2 min.	4 mA
Current input mode 2 max.	20 mA
Input current min.	0 mA

Input current max.	20 mA
Conversion time analog input per channel	0,48 ms
Diagnostics	
Diagnostic	Under voltage
Diagnostic via BUS	per module
Diagnostic via LED	per module and channel
Short circuit diagnosis	yes
LED display	Ethernet connection/data traffic
Overload diagnosis	yes
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	109 mm
Width	12,9 mm
Depth	76,5 mm
Environmental characteristics Climatic	
Operating temperature min.	0 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
Storage temperature max.	70 °C
Connection type 2	
Connection type 1	Power
Connection type 2	Power
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	8
PIN 1	n.c.
PIN 2	24 V DC
PIN 3	0 V
PIN 4	24 V DC Sys
PIN 5	n.c.
PIN 6	24 V DC
PIN 7	0 V
PIN 8	0 V Sys
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	8
PIN 1	+ AI 0
PIN 2	- AI 0
PIN 3	+ AI 2
PIN 4	- AI 2
PIN 5	+ AI 1
PIN 6	- AI 1
PIN 7	+ AI 3
PIN 8	- AI 3