

RMME 11/48 AC/DC INPUT RELAY

Product discontinued, no alternative

1 relay; 1 NO contact
6 A
48 V AC/DC
Screw terminals

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료	
ECLASS-6.0	27371001
ECLASS-7.0	27371001
ECLASS-8.0	27371001
ECLASS-9.0	27371001
ETIM-5.0	EC001437
GTIN	4048879027472

세번부호	85364900
포장단위	1
Electrical data Input	
Input voltage AC	48 V
Input voltage AC min.	40 V
Input voltage AC max.	53 V
Input voltage DC	48 V
Input voltage DC min.	40 V
Input voltage DC max.	53 V
Input current	10 mA
Electrical data Output	
Utilization category AC-15 (EN IEC 60947-5-1) 4 A @ 24 V, 4 A @ 110 V, 4 A @ 230 V	
Utilization category DC-13 (EN IEC 60947-5-1) 2 A @ 24 V, 0,25 A @ 110 V, 0,1 A @ 230 V	
Switching frequency max.	15 Hz
Power rating AC max.	1500 VA
Power rating DC max.	120 W
Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current DC	1 mA
Switching current max.	6 A
Switching capacity AC-12 (EN IEC 60947-5-1) 6 A (24/110/230 V AC)	
Diagnostics	
Status indication LED	yellow
Device protection	
Condition lifetime	load-dependent
Device protection Electrical	
Rated surge voltage	1,5 kV
Electrical lifetime	100000000 Cycles
Device protection Mechanical	
Mechanical endurance	100000000 Cycles
Mechanical data	
Drop-out time max.	10 ms
Response time max.	10 ms
Bounce time max.	1 ms
Mechanical data Material data	
Material contact	AG Ni hv
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, G32, (EN 60715)
Height	56 mm
Width	12 mm
Depth	65 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Connection type 2	
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	2

PIN 1	13
PIN 2	14
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	2
PIN 1	A 1
PIN 2	A 2