


Miro off-delay Zeitrelais max.3-300 sec.

MIRO 6.2 TIMER OFF-DELAY

Relay output  
Switch-off delay: 3...300 s  
Screw terminals  
safe separation (EN 60947-1)

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료

|             |               |
|-------------|---------------|
| ECLASS-6.0  | 27210990      |
| ECLASS-6.1  | 27371790      |
| ECLASS-7.0  | 27371790      |
| ECLASS-8.0  | 27371605      |
| ECLASS-9.0  | 27371605      |
| ECLASS-10.1 | 27371605      |
| ECLASS-11.1 | 27371605      |
| ECLASS-12.0 | 27371605      |
| ETIM-5.0    | EC001439      |
| GTIN        | 4048879026970 |
| 세번부호        | 85364900      |
| 포장단위        | 1             |

Electrical data | Input

|                         |        |
|-------------------------|--------|
| Input voltage DC        | 24 V   |
| Input voltage DC min.   | 20,4 V |
| Input voltage DC max.   | 26,4 V |
| Input current           | 20 mA  |
| Input current DC max.   | 10 mA  |
| Control voltage DC      | 24 V   |
| Control voltage DC min. | 20,4 V |
| Control voltage DC max. | 26,4 V |

|                                               |                                          |
|-----------------------------------------------|------------------------------------------|
| Control current                               | 5 mA                                     |
| Electrical data   Output                      |                                          |
| Output voltage adjustable                     | no                                       |
| Output current max.                           | 6 A                                      |
| Utilization category AC-12 (EN IEC 60947-5-1) | 6 A @ 24, 6 A @ 110 V, 6 A @ 230 V       |
| Utilization category AC-15 (EN IEC 60947-5-1) | 3 A @ 24 V, 3 A @ 110 V, 3 A @ 230 V     |
| Utilization category DC-13 (EN IEC 60947-5-1) | 1 A @ 24 V, 0,2 A @ 110 V, 0,1 A @ 230 V |
| Switching frequency max.                      | 10 Hz                                    |
| Power rating AC max.                          | 1500 VA                                  |
| Power rating DC max.                          | 120 W                                    |
| Switching voltage AC max.                     | 250 V                                    |
| Switching voltage DC max.                     | 250 V                                    |
| Switching current DC                          | 100 mA                                   |
| Device protection                             |                                          |
| Condition lifetime                            | load-dependent                           |
| Device protection   Electrical                |                                          |
| Rated surge voltage                           | 4 kV                                     |
| Electrical lifetime                           | 20000000 Cycles                          |
| Device protection   Mechanical                |                                          |
| Mechanical endurance                          | 20000000 Cycles                          |
| Mechanical data                               |                                          |
| Drop-out time max.                            | 15 ms                                    |
| Response time max.                            | 10 ms                                    |
| Bounce time max.                              | 1,5 ms                                   |
| Mechanical data   Material data               |                                          |
| Material contact                              | Ag Sn O2                                 |
| Mechanical data   Mounting data               |                                          |
| Mounting method                               | geschnappt                               |
| Suitable for mounting type                    | mounting rail, (EN 60715)                |
| Height                                        | 91 mm                                    |
| Width                                         | 6,2 mm                                   |
| Depth                                         | 71 mm                                    |
| Environmental characteristics   Climatic      |                                          |
| Operating temperature min.                    | 0 °C                                     |
| Operating temperature max.                    | 55 °C                                    |
| Connection type 5                             |                                          |
| Connection                                    | Screw terminals SK                       |
| Family construction form                      | terminal                                 |
| Gender                                        | female                                   |
| Color contact carrier                         | green                                    |
| No. of poles                                  | 1                                        |
| PIN 1                                         | + A 1                                    |
| Connection                                    | Screw terminals SK                       |
| Family construction form                      | terminal                                 |
| Gender                                        | female                                   |
| Color contact carrier                         | green                                    |
| No. of poles                                  | 1                                        |
| PIN 1                                         | 18                                       |
| Connection                                    | Screw terminals SK                       |
| Family construction form                      | terminal                                 |

|                          |                    |
|--------------------------|--------------------|
| Gender                   | female             |
| Color contact carrier    | green              |
| No. of poles             | 1                  |
| PIN 1                    | 17                 |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| Color contact carrier    | green              |
| No. of poles             | 1                  |
| PIN 1                    | + B 1              |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| Color contact carrier    | green              |
| No. of poles             | 1                  |
| PIN 1                    | - A 2              |