

MET 1-PHASE CONTROL AND ISOLATION TRANSFORMER

P: 2000VA IN: 400VAC+/- 5% OUT: 230VAC

Single-phase - Control and Isolation Transformers  
2000 VA  
Isolation class T 40/B

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



| 제품자료        |          |
|-------------|----------|
| ECLASS-6.0  | 27031302 |
| ECLASS-6.1  | 27031302 |
| ECLASS-7.0  | 27031302 |
| ECLASS-8.0  | 27031302 |
| ECLASS-9.0  | 27031302 |
| ECLASS-10.1 | 27031302 |

|                                          |                                               |
|------------------------------------------|-----------------------------------------------|
| ECLASS-11.1                              | 27031302                                      |
| ECLASS-12.0                              | 27031302                                      |
| ETIM-5.0                                 | EC002486                                      |
| GTIN                                     | 4048879078825                                 |
| 세번부호                                     | 85043200                                      |
| 포장단위                                     | 1                                             |
| Electrical data   Supply                 |                                               |
| Power frequency                          | 50 ... 60 Hz                                  |
| Electrical data   Input                  |                                               |
| Input voltage AC                         | 400 V                                         |
| Input voltage AC min.                    | 380 V                                         |
| Input voltage AC max.                    | 420 V                                         |
| Current input AC                         | 5,1 A                                         |
| Max. inrush current                      | 76 A                                          |
| Short-circuit current                    | 182 A                                         |
| Electrical data   Output                 |                                               |
| Output voltage AC                        | 230 V                                         |
| Output voltage adjustable                | no                                            |
| Power rating AC max.                     | 2000 VA                                       |
| Device protection   Electrical           |                                               |
| Insulation test voltage input - output   | 4 kV                                          |
| Mechanical data   Mounting data          |                                               |
| Suitable for mounting type               | Long-hole mounting                            |
| Mounting dimension a                     | 200 mm                                        |
| Mounting dimension b                     | 174 mm                                        |
| Mounting dimension c                     | 9 mm                                          |
| Height                                   | 170 mm                                        |
| Width                                    | 195 mm                                        |
| Depth                                    | 250 mm                                        |
| Diameter bore                            | 9 mm                                          |
| Length bore                              | 14 mm                                         |
| Environmental characteristics   Climatic |                                               |
| Operating temperature min.               | -20 °C                                        |
| Operating temperature max.               | 40 °C                                         |
| Storage temperature min.                 | -40 °C                                        |
| Storage temperature max.                 | 80 °C                                         |
| Conformity                               |                                               |
| Product standard                         | EN 61558-1, EN 61558-2-4, EN 62041 category 0 |