

MIRO 6.2 PLUGGABLE COMPL.MODULE OUTPUT RELAY

IN: 12 VAC/DC - OUT: 250 VAC/30VDC / 6 A

- 1 NO/NC contact
- 6 A
- 12 V AC/DC
- Spring clamp terminals

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



| 제품자료        |          |
|-------------|----------|
| ECLASS-6.0  | 27371601 |
| ECLASS-6.1  | 27371601 |
| ECLASS-7.0  | 27371601 |
| ECLASS-8.0  | 27371601 |
| ECLASS-9.0  | 27371601 |
| ECLASS-10.1 | 27371601 |

|                                               |                                          |
|-----------------------------------------------|------------------------------------------|
| ECLASS-11.1                                   | 27371601                                 |
| ECLASS-12.0                                   | 27371601                                 |
| ETIM-5.0                                      | EC001437                                 |
| GTIN                                          | 4048879021340                            |
| 세번부호                                          | 85364900                                 |
| 포장단위                                          | 1                                        |
| Electrical data   Input                       |                                          |
| Input voltage AC min.                         | 9,8 V                                    |
| Input voltage AC max.                         | 14 V                                     |
| Input voltage DC min.                         | 9,8 V                                    |
| Input voltage DC max.                         | 14 V                                     |
| Input current                                 | 14,2 mA                                  |
| Electrical data   Output                      |                                          |
| Utilization category AC-12 (EN IEC 60947-5-1) | 6 A @ 24, 6 A @ 110 V, 6 A @ 230 V       |
| Utilization category AC-15 (EN IEC 60947-5-1) | 3 A @ 24 V, 3 A @ 110 V, 1,5 A @ 230 V   |
| Utilization category DC-13 (EN IEC 60947-5-1) | 1 A @ 24 V, 0,2 A @ 110 V, 0,1 A @ 230 V |
| Switching frequency max.                      | 10 Hz                                    |
| Power rating AC max.                          | 1500 VA                                  |
| Power rating DC max.                          | 180 W                                    |
| Switching voltage AC max.                     | 250 V                                    |
| Switching voltage DC max.                     | 30 V                                     |
| Switching current DC                          | 100 mA                                   |
| Switching current max.                        | 6 A                                      |
| Diagnostics                                   |                                          |
| Status indication LED                         | green                                    |
| Device protection                             |                                          |
| Condition lifetime                            | load-dependent                           |
| Device protection   Electrical                |                                          |
| Degree of protection (EN IEC 60529)           | IP20                                     |
| Rated insulation voltage                      | 250 V                                    |
| Electrical lifetime NC                        | 10000 Cycles                             |
| Electrical lifetime NO                        | 30000 Cycles                             |
| Device protection   Mechanical                |                                          |
| Mechanical endurance                          | 10000000 Cycles                          |
| Mechanical data                               |                                          |
| Drop-out time max.                            | 4 ms                                     |
| Response time max.                            | 8 ms                                     |
| Mechanical data   Material data               |                                          |
| Material contact                              | Ag Sn O2                                 |
| Mechanical data   Mounting data               |                                          |
| Mounting method                               | geschnappt                               |
| Suitable for mounting type                    | mounting rail, (EN 60715)                |
| Height                                        | 93 mm                                    |
| Width                                         | 6,2 mm                                   |
| Depth                                         | 75,6 mm                                  |
| Environmental characteristics   Climatic      |                                          |
| Operating temperature min.                    | -25 °C                                   |
| Operating temperature max.                    | 60 °C                                    |