



MDD DC/DC-CONVERTOR SWITCH MODE

IN: 24VDC OUT: 12V/0,7ADC

INPUT: 24 V DC
OUTPUT: 12 V DC
Output rating: 8 W
Current: 0.7 A
Condensation not permitted
Restart after overload by removing supply voltage

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료

ECLASS-6.0	27210901
ECLASS-6.1	27210901
ECLASS-7.0	27210901
ECLASS-8.0	27210901

ECLASS-9.0	27210901
ECLASS-10.1	27210901
ECLASS-11.1	27210901
ECLASS-12.0	27210901
ETIM-5.0	EC002540
GTIN	4048879079549
세번부호	85043121
포장단위	1

Electrical data

Security level	SELV
----------------	------

Electrical data | Input

Fuse protection primary side internal	1,5 A
Characteristic back-up fuse	Inertia
Input voltage DC	24 V
Current input AC	0,6 A

Electrical data | Output

Output voltage DC	12 V
Output voltage DC min.	11,76 V
Output voltage DC max.	12,24 V
Output voltage adjustable	no
Output current max.	0,7 A
Ripple max.	0,2 %

Device protection | Electrical

Overload resistant	yes
Short-circuit protected	yes
Insulation test voltage input - output	4 kV

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, G32, (EN 60715)

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	50 °C

Conformity

Low Voltage Directive	EN 61204-3
-----------------------	------------

Connection type 1

Connection type 1	Output
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	4
PIN 1	+
PIN 2	+
PIN 3	-
PIN 4	-