



MST 1-PHASE CONTROL AND ISOLATION TRANSFORMER

P: 2500VA IN: 208...550VAC OUT: 2x115VAC

Single-phase - Control and Isolation Transformers  
2500 VA  
Isolation class T 40/B  
Other voltages on request.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



| 제품자료        |          |
|-------------|----------|
| ECLASS-6.0  | 27031302 |
| ECLASS-6.1  | 27031302 |
| ECLASS-7.0  | 27031302 |
| ECLASS-8.0  | 27031302 |
| ECLASS-9.0  | 27031302 |
| ECLASS-10.1 | 27031302 |

|                                          |                                                       |
|------------------------------------------|-------------------------------------------------------|
| ECLASS-11.1                              | 27031302                                              |
| ECLASS-12.0                              | 27031302                                              |
| ETIM-5.0                                 | EC002486                                              |
| GTIN                                     | 4048879078696                                         |
| 세번부호                                     | 85043200                                              |
| 포장단위                                     | 1                                                     |
| Electrical data   Supply                 |                                                       |
| Power frequency                          | 50 ... 60 Hz                                          |
| Electrical data   Input                  |                                                       |
| Input voltage 1 AC                       | 208 V                                                 |
| Input voltage 2 AC                       | 550 V                                                 |
| Input voltage AC                         | 208, 230, 380, 400, 420, 440, 460, 480, 500, 525, 550 |
| Input current at input voltage 1 AC      | 12,5 A                                                |
| Input current at input voltage 2 AC      | 4,72 A                                                |
| Inrush current at input voltage 1        | 363 A                                                 |
| Inrush current at input voltage 2        | 137 A                                                 |
| Short-circuit current at input voltage 1 | 670 A                                                 |
| Short-circuit current at input voltage 2 | 254 A                                                 |
| Electrical data   Output                 |                                                       |
| Output voltage                           | 1 × 230 / 1 × 115 / 2 × 115 V AC                      |
| Output voltage AC 1                      | 230 V                                                 |
| Output voltage AC 2                      | 115 V                                                 |
| Output voltage adjustable                | yes                                                   |
| Power rating AC max.                     | 2500 VA                                               |
| Device protection   Electrical           |                                                       |
| Insulation test voltage input - output   | 4 kV                                                  |
| Mechanical data   Mounting data          |                                                       |
| Suitable for mounting type               | Schlüssellochauhängung                                |
| Mounting dimension a                     | 130 mm                                                |
| Mounting dimension b                     | 150 mm                                                |
| Mounting dimension c                     | 10 mm                                                 |
| Height                                   | 200 mm                                                |
| Width                                    | 195 mm                                                |
| Depth                                    | 217 mm                                                |
| Diameter bore                            | 10 mm                                                 |
| Length bore                              | 18 mm                                                 |
| Environmental characteristics   Climatic |                                                       |
| Operating temperature min.               | -20 °C                                                |
| Operating temperature max.               | 40 °C                                                 |
| Storage temperature min.                 | -40 °C                                                |
| Storage temperature max.                 | 80 °C                                                 |
| Conformity                               |                                                       |
| Product standard                         | EN 61558-1, EN 61558-2-4, EN 62041 category 0         |
| Connection type 5                        |                                                       |
| Connection type 1                        | Input                                                 |
| Connection type 2                        | Input                                                 |
| Connection type 3                        | Output                                                |
| Connection type 4                        | Output                                                |
| Connection                               | Screw terminals SK                                    |
| Family construction form                 | terminal                                              |
| Gender                                   | female                                                |

|                          |                      |
|--------------------------|----------------------|
| No. of poles             | 8                    |
| PIN 1                    | 1                    |
| PIN 2                    | 2                    |
| PIN 3                    | 3                    |
| PIN 4                    | 4                    |
| PIN 5                    | 5                    |
| PIN 6                    | 6                    |
| PIN 7                    | 7                    |
| PIN 8                    | 8                    |
| Connection               | Plug-in terminals RK |
| Family construction form | terminal             |
| Gender                   | female               |
| No. of poles             | 8                    |
| PIN 1                    | 1                    |
| PIN 2                    | 2                    |
| PIN 3                    | 3                    |
| PIN 4                    | 4                    |
| PIN 5                    | 5                    |
| PIN 6                    | 6                    |
| PIN 7                    | 7                    |
| PIN 8                    | 8                    |
| Connection               | Screw terminals SK   |
| Family construction form | terminal             |
| Gender                   | female               |
| No. of poles             | 4                    |
| PIN 1                    | 9                    |
| PIN 2                    | 10                   |
| PIN 3                    | 11                   |
| PIN 4                    | 12                   |
| Connection               | Plug-in terminals RK |
| Family construction form | terminal             |
| Gender                   | female               |
| No. of poles             | 4                    |
| PIN 1                    | 9                    |
| PIN 2                    | 10                   |
| PIN 3                    | 11                   |
| PIN 4                    | 12                   |
| Connection               | Screw terminals SK   |
| Family construction form | terminal             |
| Gender                   | female               |
| Color contact carrier    | metallic             |
| No. of poles             | 1                    |
| PIN 1                    | PE                   |