


MTS SINGLE-PHASE SAFETY TRANSFORMER

P:25VA IN:400/440/460/480VAC OUT:2x18VAC

Single-phase - Control and Isolation Transformers
25 VA
Isolation class T 50/B
Other voltages on request.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료	
ECLASS-6.0	27031202
ECLASS-6.1	27031302
ECLASS-7.0	27031302
ECLASS-8.0	27031302
ECLASS-9.0	27031302
ECLASS-10.1	27031302

ECLASS-11.1	27031302
ECLASS-12.0	27031302
ETIM-5.0	EC002486
GTIN	4048879324595
세번부호	85043180
포장단위	1
Electrical data Supply	
Power frequency	50 ... 60 Hz
Electrical data Input	
Input voltage 1 AC	400 V
Input voltage 2 AC	480 V
Input voltage AC	400, 440, 460, 480
Input current at input voltage 1 AC	0,094 A
Input current at input voltage 2 AC	0,078 A
Inrush current at input voltage 1	0,6 A
Inrush current at input voltage 2	0,5 A
Short-circuit current at input voltage 1	0,7 A
Short-circuit current at input voltage 2	0,57 A
Electrical data Output	
Output voltage	2 × 18 V AC
Output voltage AC	18 V
Output voltage adjustable	no
Power rating AC max.	25 VA
Device protection Electrical	
Insulation test voltage input - output	6 kV
Mechanical data Mounting data	
Suitable for mounting type	Long-hole mounting
Mounting dimension a	56 mm
Mounting dimension b	56 mm
Mounting dimension c	4,8 mm
Height	82 mm
Width	78 mm
Depth	95 mm
Diameter bore	4,8 mm
Length bore	8,4 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	50 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C
Conformity	
Product standard	EN 61558-2-4, EN 61558-2-6, EN 62041 category 0
Connection type 3	
Connection type 1	Input
Connection type 2	Output
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	5
PIN 2	400 V
PIN 3	440 V

PIN 4	460 V
PIN 5	480 V
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	4
PIN 2	18 V
PIN 4	18 V
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	metallic
No. of poles	1
PIN 1	PE