


Cube67 Valve-Interface, I/O Extension Module

DO8, Festo CPV (9), Sub-D 9 pol., 0,6m

Expansion module  
DO8 - Valve (E) 0.5 m  
Multipole plug (70 mA)  
FESTO - CPV (SUB-D9)  
Connection cables are in the online shop under "Connection Technology".  
Housing fully potted.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



| 제품자료                     |               |
|--------------------------|---------------|
| ECLASS-6.0               | 27242604      |
| ECLASS-6.1               | 27242604      |
| ECLASS-7.0               | 27242604      |
| ECLASS-8.0               | 27242604      |
| ECLASS-9.0               | 27242604      |
| ECLASS-10.1              | 27242604      |
| ECLASS-11.1              | 27242604      |
| ECLASS-12.0              | 27242604      |
| ETIM-5.0                 | EC001599      |
| GTIN                     | 4048879045087 |
| 세번부호                     | 85389099      |
| 포장단위                     | 1             |
| Electrical data   Supply |               |
| Norm operating voltage   | EN 61131-2    |
| Operating voltage UA DC  | 24 V          |
| Current consumption max. | 50 mA         |
| Total current UA max.    | 4 A           |
| Total current US max.    | 4 A           |
| Electrical data   Output |               |

|                                          |                                  |
|------------------------------------------|----------------------------------|
| Overload resistant                       | yes                              |
| Short-circuit protected                  | yes                              |
| Output current per pin max.              | 0,05 A                           |
| Diagnostics                              |                                  |
| Actuator warning                         | per channel via BUS              |
| Diagnostic                               | No voltage, Under voltage        |
| Diagnostic via BUS                       | per module and channel           |
| Diagnostic via LED                       | per module                       |
| Short circuit diagnosis                  | yes                              |
| LED display                              | Ethernet connection/data traffic |
| Overload diagnosis                       | yes                              |
| Device protection   Electrical           |                                  |
| Degree of protection (EN IEC 60529)      | IP67                             |
| Mechanical data   Mounting data          |                                  |
| Suitable for mounting type               | 2-hole screw mounting            |
| Height                                   | 150 mm                           |
| Width                                    | 30 mm                            |
| Depth                                    | 34,5 mm                          |
| Environmental characteristics   Climatic |                                  |
| Operating temperature min.               | 0 °C                             |
| Operating temperature max.               | 55 °C                            |
| Storage temperature min.                 | -20 °C                           |
| Storage temperature max.                 | 75 °C                            |
| Connection type 3                        |                                  |
| Connection type 1                        | Bus In                           |
| Connection type 2                        | Bus Out                          |
| Connection type 3                        | Data                             |
| Family construction form                 | M12                              |
| Gender                                   | male                             |
| Color contact carrier                    | black                            |
| Coding                                   | A                                |
| No. of poles                             | 6                                |
| PIN 1                                    | 24 V DC (UA)                     |
| PIN 2                                    | 24 V DC (US)                     |
| PIN 3                                    | 0 V                              |
| PIN 4                                    | Bus internal                     |
| PIN 5                                    | Bus internal                     |
| PIN 6                                    | 0 V                              |
| Family construction form                 | M12                              |
| Gender                                   | female                           |
| Color contact carrier                    | black                            |
| Coding                                   | A                                |
| No. of poles                             | 6                                |
| PIN 1                                    | 24 V DC (UA)                     |
| PIN 2                                    | 24 V DC (US)                     |
| PIN 3                                    | 0 V                              |
| PIN 4                                    | Bus internal                     |
| PIN 5                                    | Bus internal                     |
| PIN 6                                    | 0 V                              |
| Family construction form                 | D-Sub                            |
| Gender                                   | male                             |
| No. of poles                             | 25                               |

|       |          |
|-------|----------|
| PIN 1 | Out 1    |
| PIN 2 | Out 2    |
| PIN 3 | Out 3    |
| PIN 4 | Out 4    |
| PIN 5 | Out 5    |
| PIN 6 | Out 6    |
| PIN 7 | Out 7    |
| PIN 8 | Out 8    |
| PIN 9 | 0 V Sens |