



IO-Link / analog converter

AO I 0 ... 20mA, M12, straight

IO-Link / analog converter  
AO I 0...20mA, M12  
16Bit, IP65/67, IO-Link V1.1, Class A

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



| 제품자료        |          |
|-------------|----------|
| ECLASS-6.0  | 27242601 |
| ECLASS-6.1  | 27242602 |
| ECLASS-7.0  | 27242602 |
| ECLASS-8.0  | 27242602 |
| ECLASS-9.0  | 27242602 |
| ECLASS-10.1 | 27242602 |

|                                                     |                                                                                                                                                                 |
|-----------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| ECLASS-11.1                                         | 27242602                                                                                                                                                        |
| ECLASS-12.0                                         | 27242602                                                                                                                                                        |
| ETIM-5.0                                            | EC001596                                                                                                                                                        |
| GTIN                                                | 4048879588201                                                                                                                                                   |
| 세번부호                                                | 85437090                                                                                                                                                        |
| 포장단위                                                | 1                                                                                                                                                               |
| Electrical data   Supply                            |                                                                                                                                                                 |
| Operating voltage DC                                | 24 V                                                                                                                                                            |
| Operating voltage DC min.                           | 18 V                                                                                                                                                            |
| Operating voltage DC max.                           | 30 V                                                                                                                                                            |
| Norm operating voltage                              | EN 61131-2                                                                                                                                                      |
| Operating voltage UA DC                             | 24 V                                                                                                                                                            |
| Current consumption max.                            | 19 mA                                                                                                                                                           |
| Electrical data   Output                            |                                                                                                                                                                 |
| Type Output                                         | 2-, 3-, 4-wire technology                                                                                                                                       |
| Output current max.                                 | 0,2 A                                                                                                                                                           |
| Parameterizable input averaging filter process data | yes                                                                                                                                                             |
| Conversion time analog output max.                  | 5 ms                                                                                                                                                            |
| Industrial communication   IO-Link                  |                                                                                                                                                                 |
| IO-Link process data length output                  | 2 Bytes                                                                                                                                                         |
| IO-Link revision ID                                 | V1.1                                                                                                                                                            |
| IO-Link cycle time min.                             | 2,3 ms                                                                                                                                                          |
| IO-Link transmission rate                           | COM2 (38.4 kbit/s)                                                                                                                                              |
| Port Class                                          | A                                                                                                                                                               |
| Diagnostics                                         |                                                                                                                                                                 |
| Diagnostic via IO-Link                              | yes                                                                                                                                                             |
| Diagnostic via LED                                  | yes                                                                                                                                                             |
| IO-Link events                                      | Device defect, Overcurrent sensor supply, Overtemperature, Overvoltage supply, Undervoltage supply, cable break sensor, lower limit, upper limit, Übersteuerung |
| LED display                                         | Ethernet connection/data traffic                                                                                                                                |
| Temperature control                                 | yes                                                                                                                                                             |
| Device protection   Electrical                      |                                                                                                                                                                 |
| Degree of protection (EN IEC 60529)                 | IP65, IP67                                                                                                                                                      |
| Invers-polarity protection                          | yes                                                                                                                                                             |
| Short circuit protection sensor supply              | yes                                                                                                                                                             |
| Short-circuit protection output                     | yes                                                                                                                                                             |
| Resistance to loads with regenerative power         | yes                                                                                                                                                             |
| Over voltage protection                             | yes                                                                                                                                                             |
| Mechanical data   Material data                     |                                                                                                                                                                 |
| Material housing                                    | Plastic                                                                                                                                                         |
| Mechanical data   Mounting data                     |                                                                                                                                                                 |
| Height                                              | 32,3 mm                                                                                                                                                         |
| Width                                               | 77,2 mm                                                                                                                                                         |
| Depth                                               | 15 mm                                                                                                                                                           |
| Environmental characteristics   Climatic            |                                                                                                                                                                 |
| Operating temperature min.                          | -30 °C                                                                                                                                                          |
| Operating temperature max.                          | 70 °C                                                                                                                                                           |
| Storage temperature min.                            | -40 °C                                                                                                                                                          |
| Storage temperature max.                            | 85 °C                                                                                                                                                           |
| Connection type 2                                   |                                                                                                                                                                 |

|                          |                 |
|--------------------------|-----------------|
| Connection type 1        | AO              |
| Connection type 2        | IO-Link AO      |
| Family construction form | M12             |
| Gender                   | female          |
| Color contact carrier    | black           |
| Coding                   | A               |
| No. of poles             | 4               |
| PIN 1                    | + US            |
| PIN 2                    | n.c.            |
| PIN 3                    | 0 V (Analog US) |
| PIN 4                    | AOut (U / I)    |
| Family construction form | M12             |
| Gender                   | male            |
| Color contact carrier    | black           |
| Coding                   | A               |
| No. of poles             | 4               |
| PIN 1                    | 24 V DC (L +)   |
| PIN 2                    | n.c.            |
| PIN 3                    | 0 V (L -)       |
| PIN 4                    | C / Q / IO-Link |