

## M12 female 0° A-cod. with cable shielded

PUR 4x0.34 shielded gy UL/CSA 25m

Female straight  
M12, 4-pole  
shielded  
with cable sleeves

### ⚠ NOTICE ⚠

Plastic housings with good resistance against chemicals and oils.




The resistance to aggressive media should be individually tested for your application. Further details on request.

**PRODUCT WILL BE DISCONTINUED BY JUNE 2023. PLEASE HAVE A LOOK AT THE ALTERNATIVE PRODUCTS.**

Further cable lengths on request.

## 제품 링크

### 일러스트



실제 제품은 이미지와 다를 수 있습니다.



|                                          |                                       |
|------------------------------------------|---------------------------------------|
| Cable length                             | 25 m                                  |
| Side 1                                   |                                       |
| Tightening torque                        | 0,6 Nm                                |
| Mounting method                          | inserted, screwed                     |
| Family construction form                 | M12                                   |
| Thread                                   | M12 x 1                               |
| Coding                                   | A                                     |
| Material                                 | PUR                                   |
| Width across flats                       | SW13                                  |
| Degree of protection (EN IEC 60529)      | IP65, IP66K, IP67                     |
| 제품자료                                     |                                       |
| ECLASS-6.0                               | 27279218                              |
| ECLASS-6.1                               | 27279218                              |
| ECLASS-7.0                               | 27279218                              |
| ECLASS-8.0                               | 27279218                              |
| ECLASS-9.0                               | 27060311                              |
| ECLASS-10.1                              | 27060311                              |
| ECLASS-11.1                              | 27060311                              |
| ECLASS-12.0                              | 27060311                              |
| ETIM-5.0                                 | EC001855                              |
| GTIN                                     | 4048879199957                         |
| 세번부호                                     | 85444290                              |
| 포장단위                                     | 1                                     |
| Electrical data   Supply                 |                                       |
| Operating voltage AC max.                | 60 V                                  |
| Operating voltage DC max.                | 60 V                                  |
| Operating voltage AC (UL-listed)         | 30 V                                  |
| Operating voltage DC (UL-listed)         | 30 V                                  |
| Current operating per contact max.       | 4 A                                   |
| Installation   Connection                |                                       |
| Mounting set                             | M12 x 1                               |
| Device protection   Electrical           |                                       |
| Additional condition protection degree   | inserted, screwed                     |
| Pollution Degree                         | 3                                     |
| Rated surge voltage                      | 1,5 kV                                |
| Material group (IEC 60664-1)             | I                                     |
| Mechanical data   Material data          |                                       |
| Coating locking                          | Nickeled                              |
| Coating of fitting                       | nickel plated                         |
| Locking material                         | Zinc die-casting                      |
| Material screw connection                | Zinc die-casting                      |
| Mechanical data   Mounting data          |                                       |
| Mounting method                          | inserted, screwed, Shaking protection |
| Environmental characteristics   Climatic |                                       |
| Operating temperature min.               | -25 °C                                |
| Operating temperature max.               | 85 °C                                 |
| Additional condition temperature range   | depending on cable quality            |
| Conformity                               |                                       |
| Product standard                         | DIN EN 61076-2-101 (M12)              |
| Installation   Cable                     |                                       |

|                                                         |                                                                |
|---------------------------------------------------------|----------------------------------------------------------------|
| Cable identification                                    | 335                                                            |
| Jacket Color                                            | gray                                                           |
| Type of Certificate                                     | cURus                                                          |
| Amount stranding                                        | 1                                                              |
| Stranding                                               | 4 wires twisted                                                |
| Cable shielding (type)                                  | copper braid, tinned                                           |
| Cable shielding (coverage)                              | 85 %                                                           |
| Banding                                                 | Fleece, Foil                                                   |
| wire arrangement                                        | brown, black, blue, white                                      |
| Cable weight                                            | 56,1 g/m                                                       |
| Material jacket                                         | PUR                                                            |
| Shore hardness jacket                                   | 85 ± 3 Shore A                                                 |
| Freedom from ingredients (jacket)                       | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Outer-diameter (jacket)                                 | 5,9 mm                                                         |
| Tolerance outer diameter (sheath)                       | ± 5 %                                                          |
| Material wire insulation                                | PP                                                             |
| Amount wires                                            | 4                                                              |
| Outer diameter insulation                               | 1,55 mm                                                        |
| Outer diameter tolerance core insulation                | ± 5 %                                                          |
| Shore hardness wire insulation                          | 72 ± 3 Shore D                                                 |
| Ingredient freeness wire insulation                     | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Amount strands (wire)                                   | 42                                                             |
| Diameter of single wires                                | 0,1 mm                                                         |
| Conductor crosssection (wire)                           | 0,34 mm²                                                       |
| Material conductor wire                                 | Stranded copper wire, bare                                     |
| Conductor type (wire)                                   | strand class 6                                                 |
| Current load capacity (standard)                        | to DIN VDE 0298-4                                              |
| Current load capacity min. wire                         | 4,8 A                                                          |
| Electrical resistance line constant wire                | 52 Ω/km @ 20 °C                                                |
| Nominal voltage power AC max.                           | 300 V                                                          |
| Power frequency withstand voltage power (wire - jacket) | 2 kV @ 60 s                                                    |
| AC withstand voltage power (wire - wire)                | 2 kV @ 60 s                                                    |
| Min. operating temperature (static)                     | -40 °C                                                         |
| Max. operating temperature (fixed)                      | 80 °C                                                          |
| Operating temperature min. (dynamic)                    | -20 °C                                                         |
| Operating temperature max. (dynamic)                    | 80 °C                                                          |
| Flame resistance                                        | IEC 60332-2-2   UL 1581 § 1100 FT2   UL 1581 § 1090            |
| chemical resistance                                     | Good, application-related testing                              |
| Gasoline resistance                                     | Good, application-related testing                              |
| Oil resistance                                          | DIN EN 60811-404   Good, application-related testing           |
| Bending radius (dynamic)                                | 10 x Outer diameter                                            |