

M12 male 0° A-cod. with cable shielded

PUR 5x0.34 shielded gy UL/CSA 2m

⚠ NOTICE ⚠

PRODUCT WILL BE DISCONTINUED BY MARCH 2023. PLEASE HAVE A LOOK AT THE ALTERNATIVE PRODUCTS.

Male straight

M12, 5-pole

shielded

with cable sleeves



Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.


Further cable lengths on request.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



Cable length	2 m
Side 1	
Tightening torque	0,6 Nm
Mounting method	inserted, screwed
Coating contact	gold plated
Family construction form	M12
Thread	M12 x 1
Coding	A
Material contact	Copper alloy
Material	PUR
No. of poles	5
Width across flats	SW13
Degree of protection (EN IEC 60529)	IP65, IP66K, IP67
Side 2	
Stripping length (jacket)	20 mm
Coating contact	gold plated
제품자료	
ECLASS-6.0	27279218
ECLASS-6.1	27279218
ECLASS-7.0	27279218
ECLASS-8.0	27279218
ECLASS-9.0	27060311
ECLASS-10.1	27060311
ECLASS-11.1	27060311
ECLASS-12.0	27060311
ETIM-5.0	EC001855
GTIN	4048879388122
세번부호	85444290
포장단위	1
Electrical data Supply	
Operating voltage AC max.	60 V
Operating voltage DC max.	60 V
Operating voltage AC (UL-listed)	30 V
Operating voltage DC (UL-listed)	30 V
Current operating per contact max.	4 A
Diagnostics	
Status indication LED	no
Installation Connection	
Stripping length (jacket)	20 mm
Mounting set	M12 x 1
Device protection Electrical	
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	1,5 kV
Material group (IEC 60664-1)	I
Mechanical data	
Contour for corrugated hose	without
Mechanical data Material data	
Coating locking	Nickeled
Coating of fitting	nickel plated
Locking material	Zinc die-casting

Material screw connection

Zinc die-casting

Mechanical data | Mounting data

Mounting method

inserted, screwed, Shaking protection

Environmental characteristics | Climatic

Operating temperature min.

-25 °C

Operating temperature max.

85 °C

Additional condition temperature range

depending on cable quality

Conformity

Product standard

DIN EN 61076-2-101 (M12)

Installation | Cable

Cable identification

351

Jacket Color

gray

Amount stranding

1

Stranding

5 wires twisted

Cable shielding (type)

copper braiding, bare

wire arrangement

brown, white, blue, black, gray

Material jacket

PUR

Outer-diameter (jacket)

6,9 mm

Tolerance outer diameter (sheath)

± 5 %

Material wire insulation

PP

Amount wires

5

Conductor crossection (wire)

0,34 mm²

Current load capacity (standard)

to DIN VDE 0298-4

Min. operating temperature (static)

-40 °C

Max. operating temperature (fixed)

80 °C

Operating temperature min. (dynamic)

-20 °C

Operating temperature max. (dynamic)

80 °C

Flame resistance

UL 1581 § 1100 FT2 | UL 1581 § 1090 | IEC 60332-2-2

chemical resistance

Good, application-related testing

Gasoline resistance

Good, application-related testing

Oil resistance

Good, application-related testing | DIN EN 60811-404

Bending radius (fixed)

10 x Outer diameter

Bending radius (dynamic)

15 x Outer diameter