

M12 female recept. A-cod. front incl. nut

PP-wires 8x0.25 1m


Flange female
M12, 8-pole
Front mounting
with multi-strand wire

제품 링크


일러스트



1	WH
2	BN
3	GN
4	YE
5	GY
6	PK
7	BU
8	RD



실제 제품은 이미지와 다를 수 있습니다.



Cable length	1 m
Side 1	
Tightening torque	0,6 Nm
Mounting method	inserted, screwed
Coating contact	gold plated

Family construction form	M12
Thread	M12 x 1
Coding	A
Material contact	Copper alloy
Material	Zinc die-casting
No. of poles	8
Degree of protection (EN IEC 60529)	IP67

제품자료

ECLASS-6.0	27279220
ECLASS-6.1	27279220
ECLASS-7.0	27440103
ECLASS-8.0	27440103
ECLASS-9.0	27440103
ECLASS-10.1	27440103
ECLASS-11.1	27440103
ECLASS-12.0	27440103
ETIM-5.0	EC001855
GTIN	4048879553827
세번부호	85444290
포장단위	1

Electrical data | Supply

Operating voltage AC max.	30 V
Operating voltage DC max.	30 V
Current operating per contact max.	2 A

Diagnostics

Status indication LED	no
-----------------------	----

Installation | Connection

Mounting set	M16 x 1.5
Width across flats	SW19

Device protection | Electrical

Protection NEMA	3, 4, 6P
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	0,8 kV
Material group (IEC 60664-1)	I

Mechanical data | Material data

Coating locking	Nickeled
Coating of fitting	nickel plated
Material gasket	FKM
Locking material	Zinc die-casting
Material screw connection	Zinc die-casting

Mechanical data | Mounting data

Mounting method	Schraubgewinde
Looking techniques	Schraubgewinde

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality

Important installation notes

Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
-----------------------	---

Note on bending radius		Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Approvals		
UL 50E	yes	
Installation Cable		
Cable identification	973	
wire arrangement	white, brown, green, yellow, gray, pink, blue, red	
Material wire insulation	PUR	
Amount wires	8	
Outer diameter insulation	1,25 mm	
Conductor crossection (wire)	0,25 mm²	
Min. operating temperature (static)	-40 °C	
Max. operating temperature (fixed)	90 °C	
Operating temperature min. (dynamic)	-25 °C	
Operating temperature max. (dynamic)	90 °C	
Flame resistance	UL 1581 § 1090 IEC 60332-2-2 UL 1581 § 1100 FT2	
chemical resistance	Good, application-related testing	
Gasoline resistance	Good, application-related testing	
Oil resistance	Good, application-related testing DIN EN 60811-404	
Bending radius (fixed)	10 x Outer diameter	