

### M12 male 0° B-cod. with cable shielded

PUR 1x2xAWG24 shielded vt UL/CSA+drag ch. 7.5m

PROFIBUS

Male straight

M12, 2-pole

B-coded

shielded




Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

### 제품 링크

#### 일러스트



실제 제품은 이미지와 다를 수 있습니다.



Cable length

7,5 m

Side 1

|                                     |                   |
|-------------------------------------|-------------------|
| Tightening torque                   | 0,6 Nm            |
| Mounting method                     | inserted, screwed |
| Family construction form            | M12               |
| Thread                              | M12 x 1           |
| Coding                              | B                 |
| Material                            | PUR               |
| Width across flats                  | SW13              |
| Degree of protection (EN IEC 60529) | IP65, IP66K, IP67 |

**Side 2**

|                           |       |
|---------------------------|-------|
| Stripping length (jacket) | 20 mm |
|---------------------------|-------|

**제품자료**

|             |               |
|-------------|---------------|
| ECLASS-6.0  | 27061801      |
| ECLASS-6.1  | 27060307      |
| ECLASS-7.0  | 27060307      |
| ECLASS-8.0  | 27060307      |
| ECLASS-9.0  | 27060307      |
| ECLASS-10.1 | 27060307      |
| ECLASS-11.1 | 27060307      |
| ECLASS-12.0 | 27060307      |
| ETIM-5.0    | EC001855      |
| GTIN        | 4048879198400 |
| 세번부호        | 85444290      |
| 포장단위        | 1             |

**Electrical data | Supply**

|                                    |      |
|------------------------------------|------|
| Operating voltage AC max.          | 60 V |
| Operating voltage DC max.          | 60 V |
| Operating voltage AC (UL-listed)   | 30 V |
| Operating voltage DC (UL-listed)   | 30 V |
| Current operating per contact max. | 4 A  |

**Installation | Connection**

|                           |         |
|---------------------------|---------|
| Stripping length (jacket) | 20 mm   |
| Mounting set              | M12 x 1 |

**Device protection | Electrical**

|                                        |                   |
|----------------------------------------|-------------------|
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 1,5 kV            |
| Material group (IEC 60664-1)           | I                 |

**Mechanical data**

|                             |         |
|-----------------------------|---------|
| Contour for corrugated hose | without |
|-----------------------------|---------|

**Mechanical data | Material data**

|                           |                  |
|---------------------------|------------------|
| Coating locking           | Nickel           |
| Coating of fitting        | nickel plated    |
| Locking material          | Zinc die-casting |
| Material screw connection | Zinc die-casting |

**Mechanical data | Mounting data**

|                 |                                       |
|-----------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
|-----------------|---------------------------------------|

**Environmental characteristics | Climatic**

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

| Conformity                                              |                                                                |
|---------------------------------------------------------|----------------------------------------------------------------|
| Product standard                                        | DIN EN 61076-2-101 (M12)                                       |
| Installation   Cable                                    |                                                                |
| Cable identification                                    | 840                                                            |
| Jacket Color                                            | violet                                                         |
| Type of Certificate                                     | cURus                                                          |
| Amount stranding                                        | 1                                                              |
| Stranding                                               | 2 wires twisted                                                |
| Cable shielding (type)                                  | copper braid, tinned                                           |
| Cable shielding (coverage)                              | 70 %                                                           |
| Banding                                                 | Fleece, Foil                                                   |
| wire arrangement                                        | red, green                                                     |
| No. of bending cycles (C-track)                         | 5 Mio. @ 25 °C                                                 |
| Cable weigth                                            | 82,5 g/m                                                       |
| Material jacket                                         | TPE-V                                                          |
| Freedom from ingredients (jacket)                       | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Outer-diameter (jacket)                                 | 7,8 mm                                                         |
| Tolerance outer diameter (sheath)                       | ± 5 %                                                          |
| Material inner jacket                                   | TPE-V                                                          |
| Color (inner jacket)                                    | white                                                          |
| Amount wires                                            | 2                                                              |
| Outer diameter insulation                               | 2,55 mm                                                        |
| Outer diameter tolerance core insulation                | ± 5 %                                                          |
| Ingredient freeness wire insulation                     | lead-free, CFC-free, halogen-free                              |
| Amount strands (wire)                                   | 19                                                             |
| Diameter of single wires                                | 24 AWG                                                         |
| Conductor crosssection (wire)                           | 24 AWG                                                         |
| Material conductor wire                                 | Stranded copper wire, bare                                     |
| Traversing distance (C-track)                           | 5 m @ 25 °C   horizontal                                       |
| Current load capacity (standard)                        | to DIN VDE 0298-4                                              |
| Current load capacity min. wire                         | 3 A                                                            |
| Electrical resistance line constant wire                | 78 Ω/km @ 20 °C                                                |
| Nominal voltage power AC max.                           | 250 V                                                          |
| Electrical capacity line constant (wire - wire) (power) | 30000 pF/km                                                    |
| AC withstand voltage power (wire - shield)              | 1 kV @ 60 s                                                    |
| Power frequency withstand voltage power (wire - jacket) | 1 kV @ 60 s                                                    |
| AC withstand voltage power (wire - wire)                | 1 kV @ 60 s                                                    |
| Min. operating temperature (static)                     | -40 °C                                                         |
| Max. operating temperature (fixed)                      | 80 °C                                                          |
| Operating temperature min. (dynamic)                    | -20 °C                                                         |
| Operating temperature max. (dynamic)                    | 70 °C                                                          |
| Flame resistance                                        | UL 1581 § 1100 FT2   IEC 60332-2-2   UL 1581 § 1090            |
| chemical resistance                                     | Good, application-related testing                              |
| Gasoline resistance                                     | Good, application-related testing                              |
| Oil resistance                                          | Good, application-related testing   DIN EN 60811-404           |
| Bending radius (fixed)                                  | 10 x Outer diameter                                            |
| Bending radius (dynamic)                                | 12 x Outer diameter                                            |