



DESINA HYBRIDFIELDBUS

PUR 2x0.34 + 4x1,5 violet 2m

DESINA® ECOFAST®
Male straight – female straight
6-pole, CU
shielded
Further cable lengths on request.
Han-Brid ® a registered trademark of HARTING KGaA.
Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.

Cable length 2 m

Side 1

Mounting method inserted

Material PC

Degree of protection (EN IEC 60529) IP65

제품자료

ECLASS-6.0 27279218

ECLASS-7.0 27279218

ECLASS-8.0 27279218

ECLASS-9.0 27060311

ETIM-5.0 EC001855

GTIN 4048879186803

세번부호 85444290

포장단위 1

Electrical data | Supply

Operating voltage AC max. 24 V

Operating voltage DC max. 24 V

Current operating per contact max. 10 A

Device protection | Electrical

Additional condition protection degree inserted, screwed

Mechanical data | Material data

Material screw connection PC

Mechanical data | Mounting data

Looking techniques Clip locking

Environmental characteristics | Climatic

Operating temperature min. -25 °C

Operating temperature max. 85 °C

Additional condition temperature range depending on cable quality

Important installation notes

Note on strain relief Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.

Note on bending radius **Attention:** Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.**Installation | Cable**

Cable identification 964

Jacket Color violet

wire arrangement (black 1, black 2, black 3, black 4), (red, green)

Material jacket PUR

Outer-diameter (jacket) 10 mm

Tolerance outer diameter (sheath) $\pm 5\%$

Material inner jacket PVC

Material wire insulation PVC

Amount wires 4

Conductor crossection (wire) 1,5 mm²

Material wire insulation (Data) PVC

Amount wires (Data) 2

Conductor crossection wire (Data) 0,34 mm²

Min. operating temperature (static) -30 °C

Max. operating temperature (fixed) 70 °C

Operating temperature min. (dynamic) -40 °C

Operating temperature max. (dynamic) 60 °C

Flame resistance IEC 60332-2-2 | UL 1581 § 1100 FT2 | UL 1581 § 1090

chemical resistance Good, application-related testing

Gasoline resistance Good, application-related testing

Oil resistance Good, application-related testing | DIN EN 60811-404

Bending radius (dynamic) 8 x Outer diameter