

## MSUD double valve BI-11mm with cable

PUR 4x0.75 gy UL/CSA 7.5m

Form BI (11 mm)

24 V AC  $\pm 20\%$  / DC  $\pm 25\%$

LED and suppression

Connection cable L = 150 mm




Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

## 제품 링크

### 일러스트



실제 제품은 이미지와 다를 수 있습니다.



Cable length 7,5 m

### Side 1

Tightening torque 0,4 Nm

|                                          |                                                  |
|------------------------------------------|--------------------------------------------------|
| Thread                                   | M3                                               |
| Side 2                                   |                                                  |
| Tightening torque                        | 0,4 Nm                                           |
| Thread                                   | M3                                               |
| 제품자료                                     |                                                  |
| ECLASS-6.0                               | 27061801                                         |
| GTIN                                     | 4065909098219                                    |
| 세번부호                                     | 85444290                                         |
| 포장단위                                     | 1                                                |
| Electrical data                          |                                                  |
| Capacity CX                              | 20 ms                                            |
| Electrical data   Supply                 |                                                  |
| Operating voltage AC                     | 24 V                                             |
| Operating voltage AC min.                | 19,2 V                                           |
| Operating voltage AC max.                | 28,8 V                                           |
| Operating voltage DC                     | 24 V                                             |
| Operating voltage DC min.                | 18 V                                             |
| Operating voltage DC max.                | 30 V                                             |
| Cut-off peak voltage max.                | 55 V                                             |
| Current operating per contact max.       | 4 A                                              |
| Current consumption max.                 | 12 mA                                            |
| Diagnostics                              |                                                  |
| Status indication LED                    | yellow                                           |
| Device protection   Electrical           |                                                  |
| Degree of protection (EN IEC 60529)      | IP67                                             |
| Additional condition protection degree   | inserted, screwed                                |
| Rated surge voltage                      | 0,8 kV                                           |
| Mechanical data   Material data          |                                                  |
| Color housing                            | black                                            |
| Material housing                         | Plastic                                          |
| Mechanical data   Mounting data          |                                                  |
| Mounting method                          | inserted, screwed                                |
| Environmental characteristics   Climatic |                                                  |
| Operating temperature min.               | -25 °C                                           |
| Operating temperature max.               | 85 °C                                            |
| Additional condition temperature range   | depending on cable quality                       |
| Installation   Cable                     |                                                  |
| Cable identification                     | 227                                              |
| Cable Type                               | 2                                                |
| Printing color of wire insulation        | white (isolation black)                          |
| Jacket Color                             | gray                                             |
| Type of Certificate                      | cURus                                            |
| Amount stranding                         | 1                                                |
| Stranding                                | 4 wires twisted                                  |
| wire arrangement                         | black 1, black 2, black 3, green-yellow          |
| No. of bending cycles (C-track)          | 2 Mio. @ 25 °C                                   |
| Cable weigth                             | 74,8 g/m                                         |
| Material jacket                          | PUR                                              |
| Shore hardness jacket                    | 85 ± 5 Shore A                                   |
| Freedom from ingredients (jacket)        | lead-free, cadmium-free, CFC-free, silicone-free |

|                                          |                                                  |
|------------------------------------------|--------------------------------------------------|
| Outer-diameter (jacket)                  | 7 mm                                             |
| Tolerance outer diameter (sheath)        | ± 5 %                                            |
| Material inner jacket                    | PVC                                              |
| Color (inner jacket)                     | yellow                                           |
| Material wire insulation                 | PVC                                              |
| Amount wires                             | 4                                                |
| Outer diameter insulation                | 1,8 mm                                           |
| Outer diameter tolerance core insulation | ± 5 %                                            |
| Shore hardness wire insulation           | 43 ± 5 Shore D                                   |
| Ingredient freeness wire insulation      | lead-free, cadmium-free, CFC-free, silicone-free |
| Printing color of wire insulation        | white (isolation black)                          |
| Amount strands (wire)                    | 42                                               |
| Diameter of single wires                 | 0,15 mm                                          |
| Conductor crosssection (wire)            | 0,75 mm²                                         |
| Material conductor wire                  | Stranded copper wire, bare                       |
| Conductor type (wire)                    | strand class 6                                   |
| Electrical function wire                 | Signal                                           |
| Traversing distance (C-track)            | 5 m @ 25 °C   horizontal                         |
| Current load capacity (standard)         | to DIN VDE 0298-4                                |
| Current load capacity min. wire          | 9,6 A                                            |
| Electrical function wire                 | Signal                                           |
| Electrical resistance line constant wire | 26 Ω/km @ 20 °C                                  |
| Nominal voltage power AC max.            | 300 V                                            |
| Min. operating temperature (static)      | -30 °C                                           |
| Max. operating temperature (fixed)       | 80 °C                                            |
| Operating temperature min. (dynamic)     | -5 °C                                            |
| Operating temperature max. (dynamic)     | 80 °C                                            |
| chemical resistance                      | Good, application-related testing                |
| Gasoline resistance                      | Good, application-related testing                |
| Oil resistance                           | DIN EN 60811-404                                 |
| Bending radius (fixed)                   | 10 x Outer diameter                              |
| Bending radius (dynamic)                 | 15 x Outer diameter                              |