




7/8" female recept. front

Wires 4x0.75 0.2m

Flange female
7/8" (4-pole)
with multi-strand wire

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.

Cable length	0,2 m
Side 1	
Tightening torque	1,5 Nm
Coating contact	gold plated
Family construction form	7/8"
Thread	7/8"
Material contact	Brass
Width across flats	SW24
제품자료	
ECLASS-6.0	27279218

ECLASS-6.1	27279220
ECLASS-7.0	27440103
ECLASS-8.0	27440103
ECLASS-9.0	27440103
ECLASS-10.1	27440103
ECLASS-11.1	27440103
ECLASS-12.0	27440103
ETIM-5.0	EC001855
GTIN	4048879134651
세번부호	85444290
포장단위	1

Electrical data | Supply

Operating voltage AC max.	300 V
Operating voltage AC max. (UL-listed)	600 V
Current operating per contact max.	7 A

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP68
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	4 kV
Material group (IEC 60664-1)	III

Mechanical data | Material data

Coating housing	nickel plated
Material housing	Zinc die-casting

Mechanical data | Mounting data

Mounting method	inserted, screwed, Shaking protection
-----------------	---------------------------------------

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	85 °C
Additional condition temperature range	depending on cable quality

Important installation notes

Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.

Resistances | Cable

wire arrangement	brown, white, blue, black
Cable identification	977
wire arrangement	brown, white, blue, black
Material wire insulation	PVC
Amount wires	4
Conductor crosssection (wire)	0,75 mm²
Flame resistance	UL 1581 § 1090 UL 1581 § 1100 FT2 IEC 60332-2-2
chemical resistance	Good, application-related testing
Gasoline resistance	Good, application-related testing
Oil resistance	Good, application-related testing DIN EN 60811-404