

**M12 male 0° / M12 female 0° A-cod. shielded**

PUR 12x0.14 shielded bk UL/CSA+drag ch. 0.3m

Male straight – female straight

M12 – M12, 12-pole

shielded

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.



Further cable lengths on request.


## 제품 링크

## 일러스트



|    |           |      |
|----|-----------|------|
| 1  | brown     | C 1  |
| 2  | blue      | C 2  |
| 3  | white     | C 3  |
| 4  | green     | C 4  |
| 5  | pink      | C 5  |
| 6  | yellow    | C 6  |
| 7  | black     | C 7  |
| 8  | gray      | C 8  |
| 9  | red       | C 9  |
| 10 | violet    | C 10 |
| 11 | gray/pink | C 11 |
| 12 | red/blue  | C 12 |





실제 제품은 이미지와 다를 수 있습니다.



|                          |                   |
|--------------------------|-------------------|
| Cable length             | 0,3 m             |
| Side 1                   |                   |
| Tightening torque        | 0,6 Nm            |
| Mounting method          | inserted, screwed |
| Coating contact          | gold plated       |
| Family construction form | M12               |
| Thread                   | M12 x 1           |
| Coding                   | A                 |
| Material contact         | Copper alloy      |
| Material                 | PUR               |
| No. of poles             | 12                |
| Width across flats       | SW13              |
| Side 2                   |                   |
| Tightening torque        | 0,6 Nm            |
| Mounting method          | inserted, screwed |
| Coating contact          | gold plated       |
| Family construction form | M12               |
| Thread                   | M12 x 1           |
| Coding                   | A                 |
| Material contact         | Copper alloy      |
| Material                 | PUR               |
| No. of poles             | 12                |
| 제품자료                     |                   |
| ECLASS-6.0               | 27279218          |
| ECLASS-6.1               | 27279218          |
| ECLASS-7.0               | 27279218          |
| ECLASS-8.0               | 27279218          |
| ECLASS-9.0               | 27060311          |
| ECLASS-10.1              | 27060311          |
| ECLASS-11.1              | 27060311          |
| ECLASS-12.0              | 27060311          |
| ETIM-5.0                 | EC001855          |

|                                          |                                                                                        |
|------------------------------------------|----------------------------------------------------------------------------------------|
| GTIN                                     | 4048879554756                                                                          |
| 세번부호                                     | 85444290                                                                               |
| 포장단위                                     | 1                                                                                      |
| Electrical data   Supply                 |                                                                                        |
| Operating voltage AC max.                | 30 V                                                                                   |
| Operating voltage DC max.                | 30 V                                                                                   |
| Operating voltage AC (UL-listed)         | 30 V                                                                                   |
| Operating voltage DC (UL-listed)         | 30 V                                                                                   |
| Current operating per contact max.       | 1,5 A                                                                                  |
| Diagnostics                              |                                                                                        |
| Status indication LED                    | no                                                                                     |
| Device protection   Electrical           |                                                                                        |
| Degree of protection (EN IEC 60529)      | IP65, IP67, IP68, IP66K                                                                |
| Additional condition protection degree   | inserted, screwed                                                                      |
| Pollution Degree                         | 3                                                                                      |
| Rated surge voltage                      | 0,8 kV                                                                                 |
| Material group (IEC 60664-1)             | I                                                                                      |
| Mechanical data                          |                                                                                        |
| Contour for corrugated hose              | without                                                                                |
| Mechanical data   Material data          |                                                                                        |
| Coating locking                          | Nickeled                                                                               |
| Material gasket                          | FKM                                                                                    |
| Locking material                         | Zinc die-casting                                                                       |
| Mechanical data   Mounting data          |                                                                                        |
| Mounting method                          | inserted, screwed, Shaking protection                                                  |
| Environmental characteristics   Climatic |                                                                                        |
| Operating temperature min.               | -25 °C                                                                                 |
| Operating temperature max.               | 85 °C                                                                                  |
| Additional condition temperature range   | depending on cable quality                                                             |
| Conformity                               |                                                                                        |
| Product standard                         | DIN EN 61076-2-101 (M12)                                                               |
| Installation   Cable                     |                                                                                        |
| Cable identification                     | 706                                                                                    |
| Cable Type                               | 3                                                                                      |
| Jacket Color                             | black                                                                                  |
| Type of Certificate                      | cURus                                                                                  |
| Amount stranding                         | 1                                                                                      |
| Stranding                                | 3 wires twisted                                                                        |
| Amount stranding (type 2)                | 1                                                                                      |
| Stranding (type 2)                       | 9 wires around Stranding combination twisted                                           |
| Cable shielding (type)                   | copper braid, tinned                                                                   |
| Cable shielding (coverage)               | 80 %                                                                                   |
| Banding                                  | Fleece, Foil                                                                           |
| wire arrangement                         | gray-pink, violet, red-blue, brown, red, gray, black, yellow, pink, green, white, blue |
| No. of bending cycles (C-track)          | 5 Mio. @ 25 °C                                                                         |
| Cable weigth                             | 67,1 g/m                                                                               |
| Material jacket                          | PUR                                                                                    |
| Shore hardness jacket                    | 90 ± 5 Shore A                                                                         |
| Freedom from ingredients (jacket)        | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free                         |
| Outer-diameter (jacket)                  | 6,5 mm                                                                                 |
| Tolerance outer diameter (sheath)        | ± 5 %                                                                                  |

|                                                         |                                                                |
|---------------------------------------------------------|----------------------------------------------------------------|
| Material wire insulation                                | PP                                                             |
| Amount wires                                            | 12                                                             |
| Outer diameter insulation                               | 1 mm                                                           |
| Outer diameter tolerance core insulation                | ± 5 %                                                          |
| Shore hardness wire insulation                          | 70 ± 5 Shore D                                                 |
| Ingredient freeness wire insulation                     | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Amount strands (wire)                                   | 18                                                             |
| Diameter of single wires                                | 0,1 mm                                                         |
| Conductor crossection (wire)                            | 0,14 mm²                                                       |
| Material conductor wire                                 | Stranded copper wire, bare                                     |
| Conductor type (wire)                                   | strand class 6                                                 |
| Traversing distance (C-track)                           | 5 m @ 25 °C   horizontal                                       |
| Current load capacity (standard)                        | to DIN VDE 0298-4                                              |
| Current load capacity min. wire                         | 2 A                                                            |
| Electrical resistance line constant wire                | 138 Ω/km @ 20 °C                                               |
| Nominal voltage power AC max.                           | 300 V                                                          |
| AC withstand voltage power (wire - shield)              | 2 kV @ 60 s                                                    |
| Power frequency withstand voltage power (wire - jacket) | 2 kV @ 60 s                                                    |
| AC withstand voltage power (wire - wire)                | 2 kV @ 60 s                                                    |
| Min. operating temperature (static)                     | -40 °C                                                         |
| Max. operating temperature (fixed)                      | 80 °C / 90 °C @ 10000 h Operation                              |
| Operating temperature min. (dynamic)                    | -25 °C                                                         |
| Operating temperature max. (dynamic)                    | 80 °C / 90 °C @ 10000 h Operation                              |
| UV resistance                                           | DIN EN ISO 4892-2 A                                            |
| Flame resistance                                        | UL 1581 § 1100 FT2   IEC 60332-2-2   UL 1581 § 1090            |
| chemical resistance                                     | Good, application-related testing                              |
| Gasoline resistance                                     | Good, application-related testing                              |
| Oil resistance                                          | Good, application-related testing   DIN EN 60811-404           |
| Bending radius (fixed)                                  | 5 x Outer diameter                                             |
| Bending radius (dynamic)                                | 10 x Outer diameter                                            |
| No. of torsion cycles                                   | 2 Mio.                                                         |
| Torsion speed                                           | 35 cycles/min                                                  |
| Torsion stress                                          | ± 30 °/m                                                       |