

# **M8 male 0° / M8 female 0° A-cod. snap-in**

PUR 3x0.25 gy UL/CSA+drag ch. 2m

Male straight – female straight

M8 (Snap In) – M8 (Snap In), 3-pole




Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

## **제품 링크**

### **일러스트**





실제 제품은 이미지와 다를 수 있습니다.



|                                           |                  |
|-------------------------------------------|------------------|
| Cable length                              | 2 m              |
| Side 1                                    |                  |
| Thread                                    | M8               |
| suitable for corrugated tube (internal Ø) | 6,5 mm           |
| 제품자료                                      |                  |
| ECLASS-6.0                                | 27279218         |
| ECLASS-6.1                                | 27279218         |
| ECLASS-7.0                                | 27279218         |
| ECLASS-8.0                                | 27279218         |
| ECLASS-9.0                                | 27060311         |
| ECLASS-10.1                               | 27060311         |
| ECLASS-11.1                               | 27060311         |
| ECLASS-12.0                               | 27060311         |
| ETIM-5.0                                  | EC001855         |
| GTIN                                      | 4048879602204    |
| 세번부호                                      | 85444290         |
| 포장단위                                      | 1                |
| Electrical data   Supply                  |                  |
| Operating voltage AC max.                 | 50 V             |
| Operating voltage DC max.                 | 60 V             |
| Operating voltage AC (UL-listed)          | 30 V             |
| Operating voltage DC (UL-listed)          | 30 V             |
| Current operating per contact max.        | 4 A              |
| Device protection   Electrical            |                  |
| Degree of protection (EN IEC 60529)       | IP65             |
| Additional condition protection degree    | inserted, locked |
| Pollution Degree                          | 3                |
| Rated surge voltage                       | 1,5 kV           |
| Material group (IEC 60664-1)              | I                |
| Mechanical data   Material data           |                  |
| Material housing                          | PUR              |



|                          |                     |
|--------------------------|---------------------|
| Bending radius (fixed)   | 5 x Outer diameter  |
| Bending radius (dynamic) | 10 x Outer diameter |
| Travel speed (C-track)   | 10 Mio. @ 25 °C     |
| No. of torsion cycles    | 2 Mio.              |
| Torsion stress           | ± 180 °/m           |
| Torsion speed            | 35 cycles/min       |