



7/8" female recept. front

Wires 5x0.75 1m

Flange female  
7/8" (5-pole)  
with multi-strand wire

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.

|                          |             |
|--------------------------|-------------|
| Cable length             | 1 m         |
| Side 1                   |             |
| Tightening torque        | 1,5 Nm      |
| Coating contact          | gold plated |
| Family construction form | 7/8"        |
| Thread                   | 7/8"        |
| Material contact         | Brass       |
| Width across flats       | SW24        |
| 제품자료                     |             |
| ECLASS-6.0               | 27279218    |

|             |               |
|-------------|---------------|
| ECLASS-6.1  | 27279220      |
| ECLASS-7.0  | 27440103      |
| ECLASS-8.0  | 27440103      |
| ECLASS-9.0  | 27440103      |
| ECLASS-10.1 | 27440103      |
| ECLASS-11.1 | 27440103      |
| ECLASS-12.0 | 27440103      |
| ETIM-5.0    | EC001855      |
| GTIN        | 4048879043779 |
| 세번부호        | 85444290      |
| 포장단위        | 1             |

Electrical data | Supply

|                                    |       |
|------------------------------------|-------|
| Operating voltage AC max.          | 600 V |
| Operating voltage DC max.          | 600 V |
| Current operating per contact max. | 6 A   |

Device protection | Electrical

|                                        |                   |
|----------------------------------------|-------------------|
| Degree of protection (EN IEC 60529)    | IP68              |
| Additional condition protection degree | inserted, screwed |
| Rated surge voltage                    | 4 kV              |
| Material group (IEC 60664-1)           | III               |

Mechanical data | Material data

|                  |                  |
|------------------|------------------|
| Coating housing  | nickel plated    |
| Material housing | Zinc die-casting |

Mechanical data | Mounting data

|                 |                                       |
|-----------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
|-----------------|---------------------------------------|

Environmental characteristics | Climatic

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

Important installation notes

|                        |                                                                                                                                                       |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on strain relief  | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |

Installation | Cable

|                                          |                                                      |
|------------------------------------------|------------------------------------------------------|
| Cable identification                     | 978                                                  |
| wire arrangement                         | brown, white, blue, black, green-yellow              |
| Material wire insulation                 | PVC                                                  |
| Amount wires                             | 5                                                    |
| Outer diameter insulation                | 3,1 mm                                               |
| Outer diameter tolerance core insulation | ± 5 %                                                |
| Conductor crosssection (wire)            | 0,75 mm²                                             |
| Min. operating temperature (static)      | -25 °C                                               |
| Max. operating temperature (fixed)       | 85 °C                                                |
| Operating temperature min. (dynamic)     | -10 °C                                               |
| Operating temperature max. (dynamic)     | 50 °C                                                |
| Flame resistance                         | IEC 60332-2-2   UL 1581 § 1090   UL 1581 § 1100 FT2  |
| chemical resistance                      | Good, application-related testing                    |
| Gasoline resistance                      | Good, application-related testing                    |
| Oil resistance                           | DIN EN 60811-404   Good, application-related testing |
| Bending radius (fixed)                   | 10 x Outer diameter                                  |