


Cable drum Ø 355mm

PUR 8x0.34 gy UL/CSA+drag ch. 100m

Cable drum (100 m)  
PUR (UL/CSA)  
8× 0.34 mm²  
gray  
Suitable for robots  
suitable for C-tracks  
5 Mio.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.

| 제품자료                 |                                                    |
|----------------------|----------------------------------------------------|
| ECLASS-6.0           | 27062011                                           |
| ECLASS-6.1           | 27061801                                           |
| ECLASS-7.0           | 27061801                                           |
| ECLASS-8.0           | 27061801                                           |
| ECLASS-9.0           | 27061801                                           |
| ECLASS-10.1          | 27061801                                           |
| ECLASS-11.1          | 27061801                                           |
| ECLASS-12.0          | 27061801                                           |
| ETIM-5.0             | EC001855                                           |
| GTIN                 | 4048879719933                                      |
| 세번부호                 | 85444995                                           |
| 포장단위                 | 1                                                  |
| Installation   Cable |                                                    |
| Cable identification | 376                                                |
| Cable Type           | 3                                                  |
| Jacket Color         | gray                                               |
| Type of Certificate  | cURus                                              |
| Amount stranding     | 1                                                  |
| Stranding            | 8 wires around Core filler twisted                 |
| Filler               | yes                                                |
| wire arrangement     | brown, white, red, blue, pink, gray, yellow, green |
| Cable weigth         | 49,5 g/m                                           |

|                                                   |                                                                |
|---------------------------------------------------|----------------------------------------------------------------|
| Material jacket                                   | PUR                                                            |
| Shore hardness jacket                             | 90 ± 5 Shore A                                                 |
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Outer-diameter (jacket)                           | 6 mm                                                           |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                          |
| Material wire insulation                          | PP                                                             |
| Amount wires                                      | 8                                                              |
| Outer diameter insulation                         | 1,25 mm                                                        |
| Outer diameter tolerance core insulation          | ± 5 %                                                          |
| Shore hardness wire insulation                    | 70 ± 5 Shore D                                                 |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Traversing distance (C-track)                     | 10 m @ 25 °C   horizontal                                      |
| Amount strands (wire)                             | 42                                                             |
| Diameter of single wires                          | 0,1 mm                                                         |
| Conductor crosssection (wire)                     | 0,34 mm²                                                       |
| Material conductor wire                           | Stranded copper wire, bare                                     |
| Conductor type (wire)                             | strand class 6                                                 |
| Nominal voltage AC max.                           | 300 V                                                          |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                              |
| Current load capacity min. wire                   | 4 A                                                            |
| Electrical resistance line constant wire          | 57 Ω/km @ 20 °C                                                |
| AC withstand voltage (wire - wire)                | 2,5 kV @ 60 s                                                  |
| Power frequency withstand voltage (wire - jacket) | 2,5 kV @ 60 s                                                  |
| Min. operating temperature (static)               | -40 °C                                                         |
| Max. operating temperature (fixed)                | 80 °C / 90 °C @ 10000 h Operation                              |
| Operating temperature min. (dynamic)              | -25 °C                                                         |
| Operating temperature max. (dynamic)              | 80 °C / 90 °C @ 10000 h Operation                              |
| Flame resistance                                  | UL 1581 § 1090   UL 1581 § 1100 FT2   IEC 60332-2-2            |
| chemical resistance                               | Good, application-related testing                              |
| Gasoline resistance                               | Good, application-related testing                              |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404           |
| Bending radius (fixed)                            | 5 x Outer diameter                                             |
| Bending radius (dynamic)                          | 10 x Outer diameter                                            |
| Travel speed (C-track)                            | 10 Mio. @ 25 °C                                                |
| No. of torsion cycles                             | 2 Mio.                                                         |
| Torsion stress                                    | ± 180 °/m                                                      |
| Torsion speed                                     | 35 cycles/min                                                  |