

## M12 Power male 0° / female 0° L-cod.

PUR 5x1.5 bk UL/CSA+drag ch. 1.4m

Power

M12 – M12, 5-pole

Male straight – female straight

L-coded

with cable sleeves



Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.



Further cable lengths on request.

## 제품 링크

### 일러스트



|    |      |    |
|----|------|----|
| 1  | BN 1 | 1  |
| 2  | WH 2 | 2  |
| 3  | BU 3 | 3  |
| 4  | BK 4 | 4  |
| FE | GY 5 | FE |



실제 제품은 이미지와 다를 수 있습니다.



|                                           |                   |
|-------------------------------------------|-------------------|
| Cable length                              | 1,4 m             |
| Side 1                                    |                   |
| Tightening torque                         | 0,6 Nm            |
| Mounting method                           | inserted, screwed |
| Coating contact                           | gold plated       |
| Family construction form                  | M12P              |
| Thread                                    | M12 x 1           |
| suitable for corrugated tube (internal Ø) | 12 mm             |
| Coding                                    | L                 |
| Material contact                          | Copper alloy      |
| No. of poles                              | 5                 |
| Side 2                                    |                   |
| Tightening torque                         | 0,6 Nm            |
| Mounting method                           | inserted, screwed |
| Coating contact                           | gold plated       |
| Family construction form                  | M12P              |
| Thread                                    | M12 x 1           |
| Coding                                    | L                 |

No. of poles 5

**제품자료**

|             |               |
|-------------|---------------|
| ECLASS-6.0  | 27279218      |
| ECLASS-6.1  | 27279218      |
| ECLASS-7.0  | 27279218      |
| ECLASS-8.0  | 27279218      |
| ECLASS-9.0  | 27060327      |
| ECLASS-10.1 | 27060311      |
| ECLASS-11.1 | 27060311      |
| ECLASS-12.0 | 27060327      |
| ETIM-5.0    | EC001855      |
| GTIN        | 4065909083680 |
| 세번부호        | 85444290      |
| 포장단위        | 1             |

**Electrical data | Supply**

|                                    |      |
|------------------------------------|------|
| Operating voltage DC max.          | 63 V |
| Current operating per contact max. | 12 A |

**Installation | Connection**

|                    |      |
|--------------------|------|
| Width across flats | SW17 |
|--------------------|------|

**Device protection | Electrical**

|                                        |                   |
|----------------------------------------|-------------------|
| Degree of protection (EN IEC 60529)    | IP65, IP67        |
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 1,5 kV            |
| Material group (IEC 60664-1)           | I                 |

**Mechanical data | Material data**

|                  |                  |
|------------------|------------------|
| Coating locking  | Nickeled         |
| Material gasket  | FKM              |
| Material housing | PUR              |
| Locking material | Zinc die-casting |

**Mechanical data | Mounting data**

|                 |                                       |
|-----------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
|-----------------|---------------------------------------|

**Environmental characteristics | Climatic**

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

**Conformity**

|                  |                 |
|------------------|-----------------|
| Product standard | IEC 61076-2-111 |
|------------------|-----------------|

**Installation | Cable**

|                                   |                                                                                                                           |
|-----------------------------------|---------------------------------------------------------------------------------------------------------------------------|
| Cable identification              | P04                                                                                                                       |
| Cable Type                        | 3                                                                                                                         |
| Printing color of wire insulation | black (white isolation), white (isolation blue), white (isolation brown), white (isolation black), white (gray isolation) |
| Jacket Color                      | black                                                                                                                     |
| Type of Certificate               | cURus                                                                                                                     |
| Amount stranding                  | 1                                                                                                                         |
| Stranding                         | 5 wires around Filler twisted                                                                                             |
| Filler                            | yes                                                                                                                       |
| wire arrangement                  | gray 5, black 4, blue 3, white 2, brown 1                                                                                 |
| Traversing distance (C-track)     | 5 m @ 25 °C                                                                                                               |
| Cable weight                      | 129,8 g/m                                                                                                                 |

|                                                   |                                                                                                                           |
|---------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|
| Material jacket                                   | PUR                                                                                                                       |
| Shore hardness jacket                             | 90 ± 5 Shore A                                                                                                            |
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free                                                            |
| Outer-diameter (jacket)                           | 8,2 mm                                                                                                                    |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                                                                                     |
| Material wire insulation                          | PP                                                                                                                        |
| Amount wires                                      | 5                                                                                                                         |
| Outer diameter insulation                         | 2,3 mm                                                                                                                    |
| Outer diameter tolerance core insulation          | ± 5 %                                                                                                                     |
| Shore hardness wire insulation                    | 60 ± 5 Shore D                                                                                                            |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free                                                            |
| Printing color of wire insulation                 | black (white isolation), white (isolation blue), white (isolation brown), white (isolation black), white (gray isolation) |
| Amount strands (wire)                             | 84                                                                                                                        |
| Diameter of single wires                          | 0,15 mm                                                                                                                   |
| Conductor crosssection (wire)                     | 1,5 mm <sup>2</sup>                                                                                                       |
| Material conductor wire                           | Stranded copper wire, bare                                                                                                |
| Conductor type (wire)                             | strand class 6                                                                                                            |
| Nominal voltage AC max.                           | 1000 V                                                                                                                    |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                                                                                         |
| Current load capacity min. wire                   | 13,5 A                                                                                                                    |
| Electrical resistance line constant wire          | 13,3 Ω/km @ 20 °C                                                                                                         |
| AC withstand voltage (wire - wire)                | 10 kV @ 60 s                                                                                                              |
| Power frequency withstand voltage (wire - jacket) | 10 kV @ 60 s                                                                                                              |
| Min. operating temperature (static)               | -50 °C                                                                                                                    |
| Max. operating temperature (fixed)                | 80 °C / 90 °C @ 10000 h Operation                                                                                         |
| Operating temperature min. (dynamic)              | -25 °C                                                                                                                    |
| Operating temperature max. (dynamic)              | 80 °C / 90 °C @ 10000 h Operation                                                                                         |
| UV resistance                                     | DIN EN ISO 4892-2 A                                                                                                       |
| Flame resistance                                  | UL 1581 § 1100 FT2   UL 1581 § 1090   IEC 60332-2-2                                                                       |
| chemical resistance                               | Good, application-related testing                                                                                         |
| Gasoline resistance                               | Good, application-related testing                                                                                         |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404                                                                      |
| Bending radius (fixed)                            | 7,5 x Outer diameter                                                                                                      |
| Bending radius (dynamic)                          | 10 x Outer diameter                                                                                                       |
| Travel speed (C-track)                            | 5 Mio. @ 25 °C                                                                                                            |
| No. of torsion cycles                             | 2 Mio.                                                                                                                    |
| Torsion stress                                    | ± 180 °/m                                                                                                                 |
| Torsion speed                                     | 35 cycles/min                                                                                                             |