

B16 male 16-pole, screw t., 500 V, 16 A


B16
Male
16-pole
Screw terminal
Technical data will be only guaranteed with Murrelektronik components.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료	
ECLASS-6.0	27143424
ECLASS-6.1	27261204
ECLASS-7.0	27440205
ECLASS-8.0	27440205
ECLASS-9.0	27440205
ECLASS-10.1	27440205
ECLASS-11.1	27440205
ECLASS-12.0	27440205
ETIM-5.0	EC000438
GTIN	4048879639217
세번부호	85389099
포장단위	1
Electrical data Supply	
Operating voltage AC	500 V
Operating voltage DC	500 V
Operating current	16 A
Installation	
Connection cross section min.	0,5 mm²
Connection cross section max.	2,5 mm²
AWG number min.	20
AWG number max.	14

Installation | Connection

Stripping length	7,5 mm
Wire insulation diameter min.	3,6 mm
Connection	Screw terminals SK
Tightening torque clamping screw	0,5 Nm
Gender	male
Mating cycles min.	500

Installation | Pin assignment

No. of poles	16 + PE
--------------	---------

Device protection | Electrical

Pollution Degree	3
Rated surge voltage	6 kV
Insulation resistance min.	100 MΩ
Material group (IEC 60664-1)	IIIb
Overvoltage category (EN 60664-1)	III
Overvoltage category (EN 60950-1)	III

Mechanical data

Holding force min.	150 N
Pulling force max.	150 N

Mechanical data | Material data

Coating contact	silver-plated
Combustibility class (UL94)	V-0
Material contact	Brass
Material contact carrier	PA GF

Mechanical data | Mounting data

Size	B16
Height	33,2 mm
Width	33,9 mm
Depth	63,4 mm

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	125 °C
Climatic category (EN IEC 60068-1)	40/125/10