


Cable drum Ø 355mm

PUR 5x0.34 or UL/CSA+robot+drag ch. 100m

Cable drum (100 m)  
PUR (UL/CSA)  
5× 0.34 mm²  
orange  
suitable for C-tracks  
10 Mio.  
Suitable for robots  
±360°/m

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.

| 제품자료                 |                                         |
|----------------------|-----------------------------------------|
| ECLASS-6.0           | 27062011                                |
| ECLASS-6.1           | 27061801                                |
| ECLASS-7.0           | 27061801                                |
| ECLASS-8.0           | 27061801                                |
| ECLASS-9.0           | 27061801                                |
| ECLASS-10.1          | 27061801                                |
| ECLASS-11.1          | 27061801                                |
| ECLASS-12.0          | 27061801                                |
| ETIM-5.0             | EC001855                                |
| GTIN                 | 4048879608190                           |
| 세번부호                 | 85444995                                |
| 포장단위                 | 1                                       |
| Installation   Cable |                                         |
| Cable identification | 847                                     |
| Cable Type           | 5                                       |
| Jacket Color         | orange                                  |
| Type of Certificate  | cURus                                   |
| Amount stranding     | 1                                       |
| Stranding            | 5 wires around Core filler twisted      |
| Filler               | yes                                     |
| wire arrangement     | brown, black, blue, white, green-yellow |
| Cable weigth         | 41,8 g/m                                |

이 데이터 시트에 포함된 정보는 최대한의 주의로 작성되었습니다.  
2024-05-21

|                                                   |                                                                |
|---------------------------------------------------|----------------------------------------------------------------|
| Material jacket                                   | PUR                                                            |
| Shore hardness jacket                             | 58 ± 3 Shore D                                                 |
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Outer-diameter (jacket)                           | 5 mm                                                           |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                          |
| Material wire insulation                          | PP                                                             |
| Amount wires                                      | 5                                                              |
| Outer diameter insulation                         | 1,25 mm                                                        |
| Outer diameter tolerance core insulation          | ± 5 %                                                          |
| Shore hardness wire insulation                    | 74 ± 3 Shore D                                                 |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Amount strands (wire)                             | 42                                                             |
| Diameter of single wires                          | 0,1 mm                                                         |
| Conductor crosssection (wire)                     | 0,34 mm <sup>2</sup>                                           |
| Material conductor wire                           | Stranded copper wire, bare                                     |
| Conductor type (wire)                             | strand class 6                                                 |
| Nominal voltage AC max.                           | 300 V                                                          |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                              |
| Current load capacity min. wire                   | 4,5 A                                                          |
| Electrical resistance line constant wire          | 60 Ω/km @ 20 °C                                                |
| AC withstand voltage (wire - wire)                | 2,5 kV @ 60 s                                                  |
| Power frequency withstand voltage (wire - jacket) | 2,5 kV @ 60 s                                                  |
| Min. operating temperature (static)               | -40 °C                                                         |
| Max. operating temperature (fixed)                | 80 °C / 90 °C @ 10000 h Operation                              |
| Operating temperature min. (dynamic)              | -25 °C                                                         |
| Operating temperature max. (dynamic)              | 80 °C / 90 °C @ 10000 h Operation                              |
| Flame resistance                                  | IEC 60332-2-2   UL 1581 § 1090   UL 1581 § 1100 FT2            |
| chemical resistance                               | Good, application-related testing                              |
| Gasoline resistance                               | Good, application-related testing                              |
| Oil resistance                                    | DIN EN 60811-404   Good, application-related testing           |
| Bending radius (fixed)                            | 5 x Outer diameter                                             |
| Bending radius (dynamic)                          | 10 x Outer diameter                                            |
| No. of bending cycles (C-track)                   | 10 Mio. @ 25 °C                                                |
| Traversing distance (C-track)                     | 5 m @ 25 °C   horizontal                                       |
| Travel speed (C-track)                            | 3,3 m/s @ 25 °C                                                |
| No. of torsion cycles                             | 1 Mio.                                                         |
| Torsion stress                                    | ± 360 °/m                                                      |
| Torsion speed                                     | 35 cycles/min                                                  |