


50M MAIN CABLE PUR/PVC-JB 8\*0,34+3\*0,75

8-way distribution boxes M12  
PUR/PVC  
8× 0.34 + 3× 0.75 mm²

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료

|             |               |
|-------------|---------------|
| ECLASS-6.0  | 27062011      |
| ECLASS-6.1  | 27279218      |
| ECLASS-7.0  | 27279218      |
| ECLASS-8.0  | 27279218      |
| ECLASS-9.0  | 27060311      |
| ECLASS-10.1 | 27061801      |
| ECLASS-11.1 | 27061801      |
| ECLASS-12.0 | 27061801      |
| ETIM-5.0    | EC001578      |
| GTIN        | 4048879057226 |
| 세번부호        | 85444995      |
| 포장단위        | 1             |

Installation | Cable

|                           |                                              |
|---------------------------|----------------------------------------------|
| Cable identification      | 362                                          |
| Cable Type                | 2                                            |
| Function cable            | Hybrid, Signal, Power                        |
| Jacket Color              | gray                                         |
| Type of Certificate       | cURus                                        |
| Amount stranding          | 1                                            |
| Stranding                 | 2 wires with Filler twisted                  |
| Amount stranding (type 2) | 1                                            |
| Stranding (type 2)        | 9 wires around Stranding combination twisted |
| Filler                    | yes                                          |

|                                                   |                                                                                   |
|---------------------------------------------------|-----------------------------------------------------------------------------------|
| wire arrangement                                  | white, violet, (green, yellow, gray, pink, red, black, brown, blue, green-yellow) |
| Cable weighth                                     | 115,5 g/m                                                                         |
| Material jacket                                   | PUR                                                                               |
| Shore hardness jacket                             | 87 ± 5 Shore A                                                                    |
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, silicone-free                                  |
| Outer-diameter (jacket)                           | 8,1 mm                                                                            |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                                             |
| Material inner jacket                             | PVC                                                                               |
| Color (inner jacket)                              | gray                                                                              |
| Material wire insulation                          | PVC                                                                               |
| Amount wires                                      | 8                                                                                 |
| Outer diameter insulation                         | 1,3 mm                                                                            |
| Outer diameter tolerance core insulation          | ± 5 %                                                                             |
| Shore hardness wire insulation                    | 43 ± 5 Shore D                                                                    |
| Material properties wire insulation               | good machinability                                                                |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, silicone-free                                  |
| Amount strands (wire)                             | 19                                                                                |
| Diameter of single wires                          | 0,15 mm                                                                           |
| Conductor crosssection (wire)                     | 0,34 mm <sup>2</sup>                                                              |
| Material conductor wire                           | Stranded copper wire, bare                                                        |
| Conductor type (wire)                             | Strand class 5                                                                    |
| Material wire insulation (Power)                  | PVC                                                                               |
| Outer diameter wire insulation (Power)            | 1,8 mm                                                                            |
| Tolerance outer diameter wire insulation (Power)  | ±5 %                                                                              |
| Shore hardness wire insulation (Power)            | 43±5 Shore D                                                                      |
| Material properties wire insulation (Power)       | good machinability                                                                |
| Ingredient freeness wire insulation (Power)       | lead-free, cadmium-free, CFC-free, silicone-free                                  |
| Amount wires (Power)                              | 3                                                                                 |
| Amount strands wire (Power)                       | 24                                                                                |
| Diameter of single wires (Power)                  | 0,2 mm                                                                            |
| Wire conductor cross section (Power)              | 0,75 mm <sup>2</sup>                                                              |
| Material conductor wire (Power)                   | Stranded copper wire, bare                                                        |
| Conductor type wire (Power)                       | Strand class 5                                                                    |
| Max. rated voltage (conductor - conductor)        | 300 V                                                                             |
| Max. rated voltage (conductor - ground)           | 300 V                                                                             |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                                                 |
| Current load capacity min. wire                   | 4 A                                                                               |
| Current carrying capacity min. wire (Power)       | 7,8 A                                                                             |
| Electrical resistance line constant wire          | 57 Ω/km @ 20 °C                                                                   |
| Electrical resistance coating wire (Power)        | 26 Ω/km @20 °C                                                                    |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                                                       |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                                                       |
| Min. operating temperature (static)               | -30 °C                                                                            |
| Max. operating temperature (fixed)                | 80 °C                                                                             |
| Operating temperature min. (dynamic)              | -5 °C                                                                             |
| Operating temperature max. (dynamic)              | 70 °C                                                                             |
| Flame resistance                                  | UL 1581 § 1090   IEC 60332-2-2   UL 1581 § 1100 FT2                               |
| chemical resistance                               | Good, application-related testing                                                 |
| Gasoline resistance                               | Good, application-related testing                                                 |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404                              |
| Bending radius (fixed)                            | 5 x Outer diameter                                                                |
| Bending radius (dynamic)                          | 10 x Outer diameter                                                               |
| No. of bending cycles (C-track)                   | 2 Mio. @ 25 °C                                                                    |

|                               |                |
|-------------------------------|----------------|
| Traversing distance (C-track) | 5 m @ 25 °C    |
| Travel speed (C-track)        | 10 m/s @ 25 °C |