

## MVP-METALL, 8XM12, 5POLE, PRE-WIRED CABLE

10.0m PUR 16x0,34+5X0.75, UL/CSA

8-way, 5-pole

10.0 m

potentially separated

Replaces identical product (Art.No. 27523)





with LED for digital PNP-signals 24 V DC

Separate protection of ports 1, 3, 5, 7 or 2, 4, 6, 8 possible.

Further cable lengths on request.

## 제품 링크

### 일러스트



실제 제품은 이미지와 다를 수 있습니다.



### 제품자료

|            |          |
|------------|----------|
| ECLASS-6.0 | 27279219 |
| ECLASS-6.1 | 27279219 |
| ECLASS-7.0 | 27279219 |

|             |               |
|-------------|---------------|
| ECLASS-8.0  | 27279219      |
| ECLASS-9.0  | 27440108      |
| ECLASS-10.1 | 27440108      |
| ECLASS-11.1 | 27440108      |
| ECLASS-12.0 | 27440108      |
| ETIM-5.0    | EC002585      |
| GTIN        | 4048879352598 |
| 세번부호        | 85444290      |
| 포장단위        | 1             |

Electrical data | Supply

|                                    |      |
|------------------------------------|------|
| Operating voltage DC               | 24 V |
| Current operating per contact max. | 4 A  |

Installation | Connection

|              |         |
|--------------|---------|
| Mounting set | M12 x 1 |
|--------------|---------|

Device protection | Electrical

|                                     |                  |
|-------------------------------------|------------------|
| Degree of protection (EN IEC 60529) | IP65, IP67, IP68 |
|-------------------------------------|------------------|

Mechanical data | Material data

|                  |                  |
|------------------|------------------|
| Coating housing  | Nickel           |
| Material housing | Zinc die-casting |

Mechanical data | Mounting data

|                 |                |
|-----------------|----------------|
| Mounting method | Schraubgewinde |
|-----------------|----------------|

Environmental characteristics | Climatic

|                                        |                            |
|----------------------------------------|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 90 °C                      |
| Additional condition temperature range | depending on cable quality |

Installation | Cable

|                                          |                                                                                                                                                                                                           |
|------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Cable identification                     | 403                                                                                                                                                                                                       |
| Printing color of wire insulation        | white (isolation blue), white (isolation brown)                                                                                                                                                           |
| Jacket Color                             | gray                                                                                                                                                                                                      |
| Type of Certificate                      | cURus                                                                                                                                                                                                     |
| Amount stranding                         | 1                                                                                                                                                                                                         |
| Stranding                                | 5 wires around Core filler twisted                                                                                                                                                                        |
| Stranding factor min.                    | 70 mm                                                                                                                                                                                                     |
| Stranding factor max.                    | 70 mm                                                                                                                                                                                                     |
| Amount stranding (type 2)                | 1                                                                                                                                                                                                         |
| Stranding (type 2)                       | 16 wires counter-rotating twisted                                                                                                                                                                         |
| Stranding factor min. (type 2)           | 105 mm                                                                                                                                                                                                    |
| Stranding factor max. (type 2)           | 105 mm                                                                                                                                                                                                    |
| Banding                                  | Fleece                                                                                                                                                                                                    |
| Filler                                   | yes                                                                                                                                                                                                       |
| wire arrangement                         | (gray-pink, violet, brown-gray, black, gray-white, red, brown-yellow, pink, yellow-white, gray, brown-green, yellow, green-white, green, red-blue, white), brown 1, blue 2, brown 2, green-yellow, blue 1 |
| Cable weight                             | 253 g/m                                                                                                                                                                                                   |
| Material jacket                          | PUR                                                                                                                                                                                                       |
| Shore hardness jacket                    | 85 ± 5 Shore A                                                                                                                                                                                            |
| Freedom from ingredients (jacket)        | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free, LABS-free                                                                                                                                 |
| Outer-diameter (jacket)                  | 11,5 mm                                                                                                                                                                                                   |
| Tolerance outer diameter (sheath)        | ± 5 %                                                                                                                                                                                                     |
| Material wire insulation                 | TPE                                                                                                                                                                                                       |
| Amount wires                             | 5                                                                                                                                                                                                         |
| Outer diameter insulation                | 1,8 mm                                                                                                                                                                                                    |
| Outer diameter tolerance core insulation | ± 5 %                                                                                                                                                                                                     |

|                                                   |                                                             |
|---------------------------------------------------|-------------------------------------------------------------|
| Shore hardness wire insulation                    | 55 ± 5 Shore D                                              |
| Ingredient freeness wire insulation               | lead-free, CFC-free, halogen-free, silicone-free, LABS-free |
| Printing color of wire insulation                 | white (isolation blue), white (isolation brown)             |
| Traversing distance (C-track)                     | 1,8 m @ 25 °C                                               |
| Amount strands (wire)                             | 96                                                          |
| Diameter of single wires                          | 0,1 mm                                                      |
| Conductor crosssection (wire)                     | 0,75 mm²                                                    |
| Material conductor wire                           | Stranded copper wire, bare                                  |
| Conductor type (wire)                             | strand class 6                                              |
| Material wire insulation (Data)                   | TPE                                                         |
| Outer diameter wire insulation (Data)             | 1,4 mm                                                      |
| Tolerance outer diameter wire insulation (data)   | ± 5 %                                                       |
| Shore hardness wire insulation (Data)             | 55 ± 5 Shore D                                              |
| Ingredient freeness wire insulation (Data)        | lead-free, CFC-free, halogen-free, silicone-free, LABS-free |
| Amount wires (Data)                               | 16                                                          |
| Amount strands wire (Data)                        | 42                                                          |
| Diameter of single wires (Data)                   | 0,1 mm                                                      |
| Conductor crosssection wire (Data)                | 0,34 mm²                                                    |
| Material conductor wire (Data)                    | Stranded copper wire, bare                                  |
| Wire conductor type (Data)                        | strand class 6                                              |
| Max. rated voltage (conductor - conductor)        | 500 V                                                       |
| Max. rated voltage (conductor - ground)           | 300 V                                                       |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                           |
| Current load capacity min. wire                   | 9 A                                                         |
| Current load capacity min. Wire (Data)            | 4 A                                                         |
| Electrical resistance line constant wire          | 26 Ω/km @ 20 °C                                             |
| Electrical resistance coating wire (Data)         | 57 Ω/km @ 20 °C                                             |
| AC withstand voltage (wire - wire)                | 2 kV @ 60 s                                                 |
| Power frequency withstand voltage (wire - jacket) | 2 kV @ 60 s                                                 |
| Min. operating temperature (static)               | -40 °C                                                      |
| Max. operating temperature (fixed)                | 90 °C                                                       |
| Operating temperature min. (dynamic)              | -25 °C                                                      |
| Operating temperature max. (dynamic)              | 80 °C                                                       |
| Flame resistance                                  | UL 1581 § 1100 FT2   IEC 60332-2-2   UL 1581 § 1090         |
| chemical resistance                               | Good, application-related testing                           |
| Gasoline resistance                               | Good, application-related testing                           |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404        |
| Bending radius (installation)                     | x Outer diameter                                            |
| Bending radius (fixed)                            | 5 x Outer diameter                                          |
| Bending radius (dynamic)                          | 10 x Outer diameter                                         |
| Travel speed (C-track)                            | 5 Mio. @ 25 °C                                              |
| Connection type 2                                 |                                                             |
| Family construction form                          | free cable end                                              |
| No. of poles                                      | 16                                                          |
| Family construction form                          | M12                                                         |
| Gender                                            | female                                                      |
| Color contact carrier                             | black                                                       |
| Coding                                            | A                                                           |
| No. of poles                                      | 5                                                           |
| PIN 1                                             | +                                                           |
| PIN 2                                             | NC S 2                                                      |
| PIN 3                                             | -                                                           |
| PIN 4                                             | NO S 1                                                      |

PIN 5

PE