

CAN-PLUG-MALE (SUB-D) 90°

Screw terminals up to 1Mbps/s

Bus connection plug 90°
SUB-D9 (female), screw terminals
max. 1 Mbit/s with switchable terminal resistors
CANopen
Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.

제품자료	
ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27242692
ECLASS-11.1	27242692
ECLASS-12.0	27242692
ETIM-5.0	EC002584
GTIN	4048879049825
세번부호	85366990
포장단위	1
Electrical data	
Terminating resistor	connectable, integrated
Industrial communication	
Data transmission rate max.	1 MBit/s
Installation	
Connection cross section max.	1 mm²
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data Mounting data	
Height	65 mm

Width	48 mm
Depth	16 mm
Environmental characteristics Climatic	
Operating temperature min.	0 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
Storage temperature max.	80 °C
Important installation notes	
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.
Connection type 2	
Family construction form	D-Sub
Gender	female
No. of poles	9
PIN 2	CAN_L
PIN 3	CAN_GND
PIN 5	CAN_SHLD
PIN 6	0 V
PIN 7	CAN_H
PIN 9	CAN V +
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	6