



B6 female 6-pole, crimp t., 500 V, 16 A

B6  
Female  
6-pole  
Crimp  
Technical data will be only guaranteed with Murrelektronik components.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



| 제품자료                          |               |
|-------------------------------|---------------|
| ECLASS-6.0                    | 27143424      |
| ECLASS-6.1                    | 27261204      |
| ECLASS-7.0                    | 27440205      |
| ECLASS-8.0                    | 27440205      |
| ECLASS-9.0                    | 27440205      |
| ECLASS-10.1                   | 27440205      |
| ECLASS-11.1                   | 27440205      |
| ECLASS-12.0                   | 27440205      |
| ETIM-5.0                      | EC000438      |
| GTIN                          | 4048879637640 |
| 세번부호                          | 85366990      |
| 포장단위                          | 1             |
| Electrical data   Supply      |               |
| Operating voltage AC          | 500 V         |
| Operating voltage DC          | 500 V         |
| Operating current             | 16 A          |
| Installation                  |               |
| Connection cross section min. | 0,14 mm²      |
| Connection cross section max. | 4 mm²         |
| AWG number min.               | 26            |
| AWG number max.               | 11            |

Installation | Connection

|                               |        |
|-------------------------------|--------|
| Wire insulation diameter min. | 4,6 mm |
| Connection                    | Crimp  |
| Gender                        | female |
| Mating cycles min.            | 500    |

Installation | Pin assignment

|              |        |
|--------------|--------|
| No. of poles | 6 + PE |
|--------------|--------|

Device protection | Electrical

|                                   |        |
|-----------------------------------|--------|
| Pollution Degree                  | 3      |
| Rated surge voltage               | 6 kV   |
| Insulation resistance min.        | 100 MΩ |
| Material group (IEC 60664-1)      | IIIb   |
| Overvoltage category (EN 60664-1) | III    |
| Overvoltage category (EN 60950-1) | III    |

Mechanical data

|                    |       |
|--------------------|-------|
| Holding force min. | 150 N |
| Pulling force max. | 35 N  |

Mechanical data | Material data

|                             |               |
|-----------------------------|---------------|
| Coating contact             | silver-plated |
| Combustibility class (UL94) | V-0           |
| Material contact            | Brass         |
| Material contact carrier    | PA GF         |

Mechanical data | Mounting data

|        |         |
|--------|---------|
| Size   | B6      |
| Height | 35,6 mm |
| Width  | 33,9 mm |
| Depth  | 50,4 mm |

Environmental characteristics | Climatic

|                                    |           |
|------------------------------------|-----------|
| Operating temperature min.         | -40 °C    |
| Operating temperature max.         | 125 °C    |
| Climatic category (EN IEC 60068-1) | 40/125/10 |