



RMME 11/48 AC/DC INPUT RELAY

Product discontinued, no alternative

1 relay; 1 NO contact
6 A
48 V AC/DC
Screw terminals

Ürün Linki

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

ECLASS-6.0	27371001
ECLASS-7.0	27371001
ECLASS-8.0	27371001
ECLASS-9.0	27371001
ETIM-5.0	EC001437
GTIN	4048879027472

Gümrük tarife no (gtip) 85364900

Paket miktarı 1

Electrical data | Input

Input voltage AC 48 V

Input voltage AC min. 40 V

Input voltage AC max. 53 V

Input voltage DC 48 V

Input voltage DC min. 40 V

Input voltage DC max. 53 V

Input current 10 mA

Electrical data | Output

Utilization category AC-15 (EN IEC 60947-5-1) 4 A @ 24 V, 4 A @ 110 V, 4 A @ 230 V

Utilization category DC-13 (EN IEC 60947-5-1) 2 A @ 24 V, 0,25 A @ 110 V, 0,1 A @ 230 V

Switching frequency max. 15 Hz

Power rating AC max. 1500 VA

Power rating DC max. 120 W

Switching voltage AC max. 250 V

Switching voltage DC max. 250 V

Switching current DC 1 mA

Switching current max. 6 A

Switching capacity AC-12 (EN IEC 60947-5-1) 6 A (24/110/230 V AC)

Diagnostics

Status indication LED yellow

Device protection

Condition lifetime load-dependent

Device protection | Electrical

Rated surge voltage 1,5 kV

Electrical lifetime 100000000 Cycles

Device protection | Mechanical

Mechanical endurance 100000000 Cycles

Mechanical data

Drop-out time max. 10 ms

Response time max. 10 ms

Bounce time max. 1 ms

Mechanical data | Material data

Material contact AG Ni hv

Mechanical data | Mounting data

Mounting method geschnappt

Suitable for mounting type Mounting rail TH35, G32, (EN 60715)

Height 56 mm

Width 12 mm

Depth 65 mm

Environmental characteristics | Climatic

Operating temperature min. -20 °C

Operating temperature max. 60 °C

Connection type 2

Connection Screw terminals SK

Family construction form terminal

Gender female

No. of poles 2

PIN 1	13
PIN 2	14
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	2
PIN 1	A 1
PIN 2	A 2