


Male module, 12-pole, crimp t.
250 V (Pin-PE) / 400 V (Pin-Pin), 10 A

Male
12-pole
Crimp
Technical data will be only guaranteed with Murrelektronik components.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.

제품자료

ECLASS-6.0	27143424
ECLASS-6.1	27261204
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440217
ECLASS-10.1	27440217
ECLASS-11.1	27440217
ECLASS-12.0	27440217
ETIM-5.0	EC000438
GTIN	4048879641562
세번부호	85389099
포장단위	5

Electrical data | Supply

Operating voltage AC per power contact max.	400 V
Operating voltage AC per signal contact max.	250 V
Operating voltage DC per power contact max.	400 V
Operating voltage DC per signal contact max.	250 V
Operating current	10 A

Installation

Connection cross section min.	0,14 mm²
Connection cross section max.	2,5 mm²
AWG number min.	26
AWG number max.	13

Installation | Connection

Wire insulation diameter min.	3,7 mm
Connection	Crimp
Gender	male
Mating cycles min.	500
Installation Pin assignment	
No. of poles	12
Device protection Electrical	
Pollution Degree	3
Rated surge voltage	4 kV
Insulation resistance min.	100 MΩ
Overvoltage category (EN 60664-1)	III
Overvoltage category (EN 60950-1)	III
Mechanical data	
Holding force contacts min.	70 N
Holding force modules min.	150 N
Pulling force max.	60 N
Mechanical data Material data	
Coating contact	versilbert, vergoldet
Combustibility class (UL94)	V-0
Material housing	PA
Material contact	Brass
Mechanical data Mounting data	
Number of module slots	1
Height	44 mm
Width	14,5 mm
Depth	34,4 mm
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	125 °C
Climatic category (EN IEC 60068-1)	40/125/10