MURR ELEKTRONIK
stay connected

RMIE 11/24 INPUT RELAY

IN: 24 VDC - OUT: 125 VAC/DC / 1 A


1 relay; 1 NO/NC contact
1 A
24 V DC
Screw terminals

Ürün Linki

örnekleme



Ürün Image farklı olabilir



Ticari bilgiler	
ECLASS-6.0	27371001
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-8.0	27371601
ECLASS-9.0	27371601
ECLASS-10.1	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ETIM-5.0	EC001437
GTIN	4048879027403
Gümrük tarife no (gtip)	85364900
Paket miktarı	1

Electrical data | Input	
Input voltage DC	24 V
Input voltage DC min.	19,2 V
Input voltage DC max.	30 V
Input current	12 mA

Electrical data | Output	
Utilization category AC-15 (EN IEC 60947-5-1)	0,5 A @ 50 V
Additional condition switching frequency	with load

Bu veri sayfasındaki bilgiler en büyük özenle hazırlandı.
Bilgilerin doğruluğu bütünlüğü ve güncelliği konusunda yükümlülük ihmali sınırlıdır. Sürüm: 2024-03-29

Switching frequency max.	0,1 Hz
Power rating AC max.	60 VA
Power rating DC max.	30 W
Switching voltage AC max.	125 V
Switching voltage DC max.	125 V
Switching current DC	1 mA
Switching current max.	1 A
Switching capacity AC-12 (EN IEC 60947-5-1)	1 A (50 V AC)
Switching capacity DC-13 (EN IEC 60947-5-1)	0.25 A (50 V)
Diagnostics	
Status indication LED	yellow
Device protection	
Condition lifetime	load-dependent
Device protection | Electrical	
Rated surge voltage	1,5 kV
Electrical lifetime	200000000 Cycles
Device protection | Mechanical	
Mechanical endurance	200000000 Cycles
Mechanical data	
Drop-out time max.	15 ms
Response time max.	10 ms
Bounce time max.	2 ms
Mechanical data | Material data	
Material contact	Pd Ni-Au Rh
Mechanical data | Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Environmental characteristics | Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C
Connection type 2	
Connection type 1	X1
Connection type 2	X2
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	3
PIN 1	A 1
PIN 2	A 2
PIN 3	A 2
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	3
PIN 1	14
PIN 2	11

Bu veri sayfasındaki bilgiler en büyük özenle hazırlandı.
Bilgilerin doğruluğu bütünlüğü ve güncelliği konusunda yükümlülük ihmali sınırlıdır. Sürüm: 2024-03-29

PIN 3	12

Bu veri sayfasındaki bilgiler en büyük özenle hazırlandı.
Bilgilerin doğruluğu bütünlüğü ve güncelliği konusunda yükümlülük ihmali sınırlıdır. Sürüm: 2024-03-29